

**THM WO VIN 25.4/95.2 BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 12.7 mm, 25.4 x 95.3 mm, white / yellow
Order No.	<a href="#">1420020000</a>
Type	THM WO VIN 25.4/95.2 BL
GTIN (EAN)	4050118223514
Qty.	1 items

## THM WO VIN 25.4/95.2 BL

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0026 inch
Height	25.4 mm	Height (inches)	1 inch
Width	95.3 mm	Width (inches)	3.752 inch
Net weight	545 g		

## Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Adhesive	Polyacrylate adhesive	
Type of printing	neutral	
Version	Self-adhesive	
Width	95.3 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	white / yellow	
Halogen	Yes	
Basic material	Vinyl film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	40 x 25.4 mm	
Approval acc. to UL 969 compatible printer	No	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...80 °C	
Number per roll	1000	
Imprint	Lightning	

## Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	12.7 mm
Conductor O.D.	12.7 mm	Cross-section for connected wire	0.75 - 120 mm <sup>2</sup>

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

