

HSS-HF 19.1-38.1EL W10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 19.1 - 38.1 mm, white
Order No.	1423420000
Type	HSS-HF 19.1-38.1EL W10M
GTIN (EAN)	4050118227451
Qty.	1 items

HSS-HF 19.1-38.1EL W10M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.0591 inch
Width	60.5 mm	Width (inches)	2.3819 inch
Length	10000 mm	Length (inches)	393.7 inch
Net weight	943 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	60.5 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	white	Halogen	No
Length	10000 mm	Basic material	Polyolefine
Printed characters	without	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...105 °C	Number per roll	1

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	240 mm ²
Conductor cross-section, min.	70 mm ²	Conductor O.D., max.	38.1 mm
Conductor O.D., min.	19.1 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	19.1 - 38.1 mm
Cross-section for connected wire	70 - 240 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		