

HSS-HF 1.6-3.2 EL Y13M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 1.6 - 3.2 mm, yellow |
| Order No. | 1423230000 |
| Type | HSS-HF 1.6-3.2 EL Y13M |
| GTIN (EAN) | 4050118227420 |
| Qty. | 1 items |

HSS-HF 1.6-3.2 EL Y13M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 0.7 mm | Depth (inches) | 0.0276 inch |
| Width | 5.6 mm | Width (inches) | 0.2205 inch |
| Length | 13000 mm | Length (inches) | 511.81 inch |
| Net weight | 110 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|--|
| Type of printing | neutral | Width | 5.6 mm |
| Operating temperature range, max. | 105 °C | Operating temperature range, min. | -55 °C |
| Colour | yellow | Halogen | No |
| Length | 13000 mm | Basic material | Polyolefine |
| Printed characters | without | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -55...105 °C | Number per roll | 1 |

Conductor and cable markers

| | | | |
|-----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Conductor O.D., max. | 3.2 mm |
| Conductor O.D., min. | 1.6 mm | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Text field width | 0 mm |
| Text field height | 5.4 mm | Conductor O.D. | 1.6 - 3.2 mm |
| Cross-section for connected wire | 0.5 - 1.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings

