

RS SD26F HD UNC4.40 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Passive interface for transmitting signals from a high-density SUB-D plug-in connector with clamping yoke connection technology.

- The connection between both connectors is 1 to 1 and the range includes male and female connectors with 15 to 62 poles.
- Thanks to the metal housing of the SUB-D, these connectors are ideal for transmitting analogue signals or for connecting shielded cables.
- Tension clamp connection on demand.

General ordering data

Version	Interface, RSSD, High-density SUB-D plug-in connectors, 26-pole socket, Screw connection
Order No.	1428 140000
Type	RS SD26F HD UNC4.40 S
GTIN (EAN)	4050 118232424
Qty.	1 items

RS SD26F HD UNC4.40 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	71 mm	Depth (inches)	2.7953 inch
Height	70 mm	Height (inches)	2.7559 inch
Width	55 mm	Width (inches)	2.1654 inch
Net weight	99.98 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	7b5ffb72-271d-4c73-8b09-bd0aaee3697a

Rated data UL

Rated current I _{max}	1 A
--------------------------------	-----

Connection Data

Number of poles (control side)	26-pole socket	Connection (field side)	LL3R 5.08 mm
Earthing	No	Connection on control side	High-density SUB-D plug-in connectors

Rating data

Rated voltage	125 V AC / 175 V DC	Rated current per connection	1 A
---------------	---------------------	------------------------------	-----

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	125V AC / 175 V DC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	1.15 kV	Insulation test voltage AC	0.65 kV

Connection field

Min. wire cross-section, AWG	AWG 26	Type of connection	Screw connection
Sleeve with plastic collar, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible, max. H05(07) V-K	4 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Clamping range, max.	6 mm ²	Clamping range, min.	0.5 mm ²
Max. wire cross-section, AWG	AWG 12		

RS SD26F HD UNC4.40 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

RS SD26F HD UNC4.40 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

