

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 9.6 - 12.7 mm, 15 x 70 mm, white
Order No.	1429440000
Type	THM WO 15/70 WS
GTIN (EAN)	4050118233872
Qty.	1 ROL

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	70 mm	Width (inches)	2.7559 inch
Net weight	112 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Type of printing	neutral		
Version	Self-adhesive		
Width	70 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyester film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	30 x 15 mm		
Approval acc. to UL 969	Yes		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...150 °C		
Number per roll	500		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	9.6 mm	Text field width	15 mm
Text field height	30 mm	Conductor O.D.	9.6 - 12.7 mm
Cross-section for connected wire	0.75 - 120 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		