

## THM WO 15/140 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 22.3 - 22.3 mm, 15 x 140 mm, white
Order No.	<a href="#">1429450000</a>
Type	THM WO 15/140 WS
GTIN (EAN)	4050118233902
Qty.	1 ROL

## THM WO 15/140 WS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	196 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Adhesive	Polyacrylate adhesive	
Type of printing	neutral	
Version	Self-adhesive	
Width	140 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	70 x 15 mm	
Approval acc. to UL 969	Yes	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...150 °C	
Number per roll	500	

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	323 mm <sup>2</sup>
Conductor cross-section, min.	323 mm <sup>2</sup>	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	22.3 mm	Text field width	15 mm
Text field height	70 mm	Conductor O.D.	22.3 - 22.3 mm
Cross-section for connected wire	323 - 323 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**

