

IE-FSMZ2LY0020MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO

General ordering data

| | |
|------------|--|
| Version | Pre-assembled patch cable, crossover, LC-Duplex IP 20, LC-Duplex IP 20, 9 µm, LSZH, 20 m |
| Order No. | 1433950200 |
| Type | IE-FSMZ2LY0020MLD0LD0-X |
| GTIN (EAN) | 4050118694239 |
| Qty. | 1 items |

IE-FSMZ2LY0020MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|----------|-----------------|---------------|
| Length | 20 m | Length (inches) | 787.4016 inch |
| Net weight | 146.08 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|---------------|
| Storage temperature | -25 °C...75 °C | Operating temperature | -5 °C...75 °C |
| Installation temperature | -5 °C...50 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Fibre-optic

Fibre type Singlemode, OS1

Cable structure

| | | | |
|-----------------------|----------|------------------|-----------|
| Sheath diameter | 3*6 mm | Sheathing colour | yellow |
| Standard designations | I-V(ZN)Y | Material sheath | LSZH |
| Cable layout | ZIPCORD | Primary coating | 245.00 µm |
| Core diameter | 9 µm | | |

Plug

| | | | |
|------------|--|-----------|--|
| Plug right | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded | Plug left | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|--|-----------|--|

Plug, left

Plug left LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Plug, right


Plug right LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002607 | ETIM 9.0 | EC002607 |
| ETIM 10.0 | EC002607 | ECLASS 14.0 | 27-06-10-03 |
| ECLASS 15.0 | 27-06-10-03 | | |

Drawings

Detailed drawing




IE-FSMZ2LY0020MLD0LD0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

V0 material



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | | |
|------------|----------------------------|--|
| Type | VT SF 5/21 MC NE WS V0 | Version |
| Order No. | 1689470001 | SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm, |
| GTIN (EAN) | 4008190872571 | white |
| Qty. | 160 ST | |
| Type | VT SF 6/21 MC NE WS V0 | Version |
| Order No. | 1730560001 | SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm, |
| GTIN (EAN) | 4008190954611 | white |
| Qty. | 160 ST | |