
Data sheet

PM 2.7/2.6 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	OMNIMATE Signal - series PM, Pusher markers, 2.7 x 2.6 mm, Pitch in mm (P): 3.50 Weidmueller, yellow
Order No.	1435010000
Type	PM 2.7/2.6 MC NE GE
GTIN (EAN)	4050118239768
Qty.	960 items
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31T00:00:00+01:00

Data sheet

PM 2.7/2.6 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Height	2.7 mm	Height (inches)	0.1063 inch
Width	2.6 mm	Width (inches)	0.1024 inch
Net weight	0.11 g		

Temperatures

Operating temperature range	-40…100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.001 kg CO2 eq.

General data

Width	2.6 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	Yes	
Basic material	Polyamide 66	
Printed characters	neutral	
Number of markers per packaging unit	Form of supply	MultiCard
Recommended industries	Device manufacturer	
compatible printer	PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2	
Number of markers per combination	1 MultiCard = Pusher markers	
Operating temperature range	-40…100 °C	
Application/manufacturer	Weidmueller	

Connector markers

Pitch in mm (P)	3.50 mm

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

PM 2.7/2.6 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Drawing

