


HDC MBUS 2 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Data module, 0 V, 0 A, Number of poles: 2, Crimp connection, Male, Required plug-in slots: 1
Order No.	1428990000
Type	HDC MBUS 2 MC
GTIN (EAN)	4050118233346
Qty.	1 items

HDC MBUS 2 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	40.4 mm	Height (inches)	1.5905 inch
Width	14.5 mm	Width (inches)	0.5709 inch
Net weight	6.51 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

General data

Number of poles	2	UL 94 flammability rating	V-0
Insulation resistance	1012 Ω	Plugging cycles	≥ 500
Type	Male	Surge voltage category	III
Pollution severity	3	Basic material	Polycarbonate, glass fibre reinforced
Series	ModuPlug	Rated voltage (DIN EN 61984)	0 V
Rated impulse voltage (DIN EN 61984)	0 kV	Rated current (DIN EN 61984)	0 A
Required plug-in slots	1		

PE connection data

Connection type PE Screw connection via module frame

Version

Type of connection Crimp connection

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		

HDC MBUS 2 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

