Data sheet

PAC-HD15F-HD15F-V0-10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

Order No.	1440750100
Type	PAC-HD15F-HD15F-V0-10M
GTIN (EAN)	4099986581951
Qty.	1 items

Data sheet

PAC-HD15F-HD15F-V0-10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	1220 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General Data

Cable length	10 m	Suitable for	Analogue signals
Basic material	PVC	Cable	Cable LiYCY
Interface connector	SUBD HD female 15P	Number of poles, min.	15-pole
Outer diameter	8.7 ± 1 mm	Connector PLC side	SUBD HD female 15P
Wire cross-section	0.25 mm²		

Electrical Data

Total current, max.	3 A	High voltage test	1 KV/1s
Permissible current strength per path, max.	1 A	Rated voltage	≤ 60 Vdc ≤ 25 Vac
Resistance	≤ 80 mΩ/m	Operating voltage	≤ 60 V DC ≤ 25 V AC
Capacity (wire / wires)	300 pF/m	Capacity (wire / shield)	300 pF/m

Rated data UL

Total current, max.	3 A

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		