

PAC-HD15M-HD15F-V0-2M5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

Order No.	1440770025
Type	PAC-HD15M-HD15F-V0-2M5
GTIN (EAN)	4099986581982
Qty.	1 items

PAC-HD15M-HD15F-V0-2M5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	388 g
------------	-------

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	4bbf2c0d-0764-4fc8-bb24-9351c28c190d

General Data

Cable length	2.5 m	Suitable for	Analogue signals
Basic material	PVC	Cable	Cable LiYCY
Interface connector	SUB-D HD male 15P	Number of poles, min.	15-pole
Outer diameter	8.7 ± 1 mm	Connector PLC side	SUBD HD female 15P
Wire cross-section	0.25 mm ²		

Electrical Data

Total current, max.	3 A	High voltage test	1 KV/1s
Permissible current strength per path, max.	1 A	Rated voltage	≤ 60 Vdc ≤ 25 Vac
Resistance	≤ 80 mΩ/m	Operating voltage	≤ 60 V DC ≤ 25 V AC
Capacity wire / wires	300 pF/m	Capacity wire / shield	300 pF/m

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		