

## SAIL-M12BW-PBK38-1.5V

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

### General ordering data

Version	Bus line, M12, Number of poles: 4, 1.5 m, Socket, angled, Shielded: Yes, LED: No, Sheath material: PVC
Order No.	<a href="#">1431510150</a>
Type	SAIL-M12BW-PBK38-1.5V
GTIN (EAN)	4050118241051
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-04-29T00:00:00+02:00

## SAIL-M12BW-PBK38-1.5V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Net weight 100 g

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

### Technical specifications for cable

Cable length	1.5 m	Sheathing colour	violet
Suitable for cable carriers	No	Shielded	Yes
Insulation	PVC	Bending radius, min., moving	8 x cable diameter
Bending radius, min., stationary	4 x cable diameter	Wire cross section (Print/Online)	PUR 0.25 mm <sup>2</sup> / PVC 0.34 mm <sup>2</sup>
Sheath material	PVC	Configurable cable length	No
Hybrid cable	No	Irradiation crosslinked	No
Welding spark resistance	No	Core cross-section AWG	AWG 22
Colour coding	green, black, red, orange	Resistant to welding beads	No
Number of poles	4	Outside diameter	7.8 mm ± 0.2 mm

### General technical data

Coding	B-coded	Connection thread	M12
Contact surface	Gold-plated	LED	No
Version	Socket, angled	Housing main material	PUR
Insulation resistance	108 Ω	Nominal voltage	250 V
Nominal current	4 A	Protection degree	IP67
Plugging cycles	≥ 100	Pollution severity	3
jumpered	No	Threaded ring material	Brass, nickel-plated
Temperature range of housing	-25...+80 °C	Tightening torque	M12: 0.8 - 1.2 Nm

### Electrical properties

Insulation resistance	108 Ω	Nominal voltage	250 V
-----------------------	-------	-----------------	-------

### Plug, left

Plug left	M12, B-coded, IP67, female contact, angled 90°, Plastic, shielded
-----------	-------------------------------------------------------------------

### Plug, right

Plug right	free conductor end
------------	--------------------

**SAIL-M12BW-PBK38-1.5V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**SAIL-M12BW-PBK38-1.5V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Pole scheme**



Socket angled



Socket

**Wiring diagram**



**The ideal tool: Screwty® with torque function**



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

