

HDC MHP100 M 25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Male, silver, 25 - 25 mm ²
Order No.	1435770000
Type	HDC MHP100 M 25
GTIN (EAN)	4050118240573
Qty.	10 items

HDC MHP100 M 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Net weight

14.22 g

Temperatures

Limit temperature

-40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status

Compliant with exemption

RoHS Exemption (if applicable/known)

6c

REACH SVHC

Lead 7439-92-1

SCIP

6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø

6.55 mm

Type of connection

Crimp connection

Conductor cross-section, max.

25 mm²

Surface finish

silver

Type

Male

Production methods

turned

Stripping length, rated connection

19 mm

Version insert

MHP

Conductor cross-section, min.

25 mm²

Plugging cycles

≥ 500

Basic material

Copper alloy

Cross-section for connected wire

25 - 25 mm²

Classifications

ETIM 8.0

EC000796

ETIM 10.0

EC000796

ECLASS 15.0

27-44-02-04

ETIM 9.0

EC000796

ECLASS 14.0

27-44-02-04

Drawings

