


SF 3/12 MC NE GN V2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | |
|------------|--|
| Version | SlimFix, Conductor and cable markers, 3 - 3.7 mm, 12 x 4.6 mm, green |
| Order No. | 1444310000 |
| Type | SF 3/12 MC NE GN V2 |
| GTIN (EAN) | 4050118249637 |
| Qty. | 320 items |

SF 3/12 MC NE GN V2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 4.8 mm | Depth (inches) | 0.189 inch |
| Height | 12 mm | Height (inches) | 0.4724 inch |
| Width | 4.6 mm | Width (inches) | 0.1811 inch |
| Net weight | 0.32 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.002 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|---|-----------|--|
| Type of printing | neutral | | |
| Width | 4.6 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | green | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Size of labelling field | 12 x 4.6 mm | | |
| Recommended industries | Transportation, Machinery | | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | | |
| Operating temperature range | -40...100 °C | | |

Conductor and cable markers

| | | | |
|----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 2.5 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Conductor O.D., max. | 3.7 mm |
| Conductor O.D., min. | 3 mm | Conductor O.D. | 3 - 3.7 mm |
| Cross-section for connected wire | 1.5 - 2.5 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings

