

**IE-FSMD2UE0040MSDESDEX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

---

Assembled IE cables, FO breakout cable

**General ordering data**

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 9 µm, PUR, 40 m
Order No.	<a href="#">1449420400</a>
Type	IE-FSMD2UE0040MSDESDEX
GTIN (EAN)	4050118258530
Qty.	1 items

## IE-FSMD2UE0040MSDESDEX

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Length	40 m	Length (inches)	1574.8031 inch
Net weight	1268.08 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

## General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

## Standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

## Fibre-optic

Fibre type	Singlemode, OS 2	Attenuation	≤0.4 dB/km at 1310 nm
Insertion loss	≤ 0.5 dB	Return loss (attenuation)	≥ 40 dB

## Cable structure

Sheath diameter	6 mm	Sheathing colour	black
Material sheath	PUR	Cable layout	Break-out dragline
Primary coating	245.00 µm	Core diameter	9 µm

## Mechanical and material properties of cable

Halogen	No	Min. bending radius, repetitive	77 mm
Min. bending radius, once only	25 mm	Bending cycles	100,000

## Plug

Plug right	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded	Plug left	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
------------	--	-----------	--

## Plug, left

Plug left	SC, IP67, male contact, straight, PushPull V14,
-----------	---

**IE-FSMD2UE0040MSDESDEX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

plug, Zinc diecast,  
unshielded

**Plug, right**

Plug right SC, IP67, male contact,  
straight, PushPull V14,  
plug, Zinc diecast,  
unshielded

**Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

**Drawings**

**Detailed drawing**

---

---

---

---

## IE-FSMD2UE0040MSDESDEX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## V0 material

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

## Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

## General ordering data

Type	VT SF 5/21 MC NE WS V0	Version
Order No.	<a href="#">1689470001</a>	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 ST	
Type	VT SF 6/21 MC NE WS V0	Version
Order No.	<a href="#">1730560001</a>	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 ST	