

IE-FSMD2UE0040MSDESDEX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO breakout cable

General ordering data

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 9 µm, PUR, 40 m
Order No.	1449420400
Type	IE-FSMD2UE0040MSDESDEX
GTIN (EAN)	4050118258530
Qty.	1 items

IE-FSMD2UE0040MSDESDEX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	40 m	Length (inches)	1574.8031 inch
Net weight	1268.08 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

Standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

Fibre-optic

Fibre type	Singlemode, OS 2	Attenuation	≤0.4 dB/km at 1310 nm
Insertion loss	≤ 0.5 dB	Return loss (attenuation)	≥ 40 dB

Cable structure

Sheath diameter	6 mm	Sheathing colour	black
Material sheath	PUR	Cable layout	Break-out dragline
Primary coating	245.00 µm	Core diameter	9 µm

Mechanical and material properties of cable

Halogen	No	Min. bending radius, repetitive	77 mm
Min. bending radius, once only	25 mm	Bending cycles	100,000

Plug

Plug right	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded	Plug left	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
------------	--	-----------	--

Plug, left

Plug left	SC, IP67, male contact, straight, PushPull V14,
-----------	---

IE-FSMD2UE0040MSDESDEX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**plug, Zinc diecast,
unshielded**Plug, right**

Plug right

SC, IP67, male contact,
straight, PushPull V14,
plug, Zinc diecast,
unshielded**Classifications**

ETIM 8.0

EC002607

ETIM 9.0

EC002607

ETIM 10.0

EC002607

ECLASS 14.0

27-06-10-03

ECLASS 15.0

27-06-10-03

Drawings

Detailed drawing

