


**SAIE-M12B-3+PE-S-0.5U-M16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 4, Strand / cable length: 0.5 m, Front mounting
Order No.	<a href="#">1460310000</a>
Type	SAIE-M12B-3+PE-S-0.5U-M16
GTIN (EAN)	4050118266504
Qty.	1 items

## SAIE-M12B-3+PE-S-0.5U-M16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E307231

### Dimensions and weights

Net weight	15 g
------------	------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	bd63baef-8092-4596-90c7-5b4daa22710b

### Technical specifications for cable

PE function	No	Wire cross section (Print/Online)	AWG 16
Strand / cable length	0.5 m	Core cross-section AWG	AWG 16
Colour coding	black (1), black (2), black (3), Green/yellow	Number of poles	4

### Technical data customisable plug-in connectors

Number of poles	4	Coding	S-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Nominal voltage	630 V	Nominal current	12 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Rated current	12 A	Temperature range of housing	-40 ... +85 °C

### Standards

Connector standard	IEC 61076-2-111
--------------------	-----------------

### General data

Number of poles	4	Coding	S-coded
Connection thread	M12	Contact surface	Gold-plated
Housing main material	Zinc diecast	Type of mounting	Front mounting
Nominal voltage	630 V	Nominal current	12 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Rated current	12 A	Wire cross section (Print/Online)	AWG 16
Connection 1	M12	Connection 2	Flying wires
Strand / cable length	0.5 m	Mounting thread	M 16 x 1.5
Temperature range of housing	-40 ... +85 °C	Conductor O.D.	-

### Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

Creation date 27.02.2026 11:25:34 MEZ

Catalogue status / Drawings

Drawings

Pole scheme

