

**IE-CSQS9VE0020AQEAQE-K1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Assembled IE cables

**General ordering data**

Version	System cable, V14 hybrid (shielded), V14 hybrid (shielded), PVC, 2 m, , Hybrid
Order No.	<a href="#">1465850020</a>
Type	IE-CSQS9VE0020AQEAQE-K1
GTIN (EAN)	4050118272338
Qty.	1 items

## IE-CSQS9VE0020AQEAQE-K1

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Length	2 m	Length (inches)	78.7402 inch
Net weight	374 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...80 °C
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1

## Electrical properties

Operating voltage	300 V	Insulation resistance	> 500 MΩ
-------------------	-------	-----------------------	----------

## General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

## Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

## Cable structure

Sheathing colour	black	Cross-section	2 x 0.34 mm <sup>2</sup> + 7 x 0.5 mm <sup>2</sup>
Insulation cross-section	1.25 mm	Insulation	PP
Sheath diameter, max.	9.5 mm	Sheath diameter, min.	9.1 mm
Material sheath	PVC	Cable layout	Hybrid cable, for permanent installation
Overlap of shielding braid	85 %	Insulation diameter 2	2.15 mm

## Electrical properties of cable

Operating voltage	300 V	Insulation resistance	> 500 MΩ
-------------------	-------	-----------------------	----------

## Mechanical and material properties of cable

Min. bending radius, repetitive	10 x cable diameter	Min. bending radius, once only	5 x cable diameter
---------------------------------	---------------------	--------------------------------	--------------------

## Plug, left

Plug left	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
-----------	--

**IE-CSQS9VE0020AQEAQE-K1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Plug, right**

Plug right	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
------------	--

**Classifications**

ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

**IE-CSQS9VE0020AQEAQE-K1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Wiring**

