

**SAIE-M12S-12S-TL-HW-PG9**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Version	Built-in plugs, M12, Mounting thread: , Number of poles: 12, Strand / cable length:
Order No.	<a href="#">1467740000</a>
Type	SAIE-M12S-12S-TL-HW-PG9
GTIN (EAN)	4050118273243
Qty.	20 items

**SAIE-M12S-12S-TL-HW-PG9**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 19.65 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP bd63baef-8092-4596-90c7-5b4daa22710b

**Technical specifications for cable**

Number of poles 12

**Technical data customisable plug-in connectors**

Number of poles	12	Coding	A-coded
Contact surface	Gold-plated	Type of connection	Pin
Housing main material	Zinc diecast	Nominal voltage	30 V
Nominal current	2 A	Protection degree	IP67, when fully mounted
Cable gland	PG 9	Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)
Temperature range of housing	-40 ... +85 ° C		

**Standards**

Connector standard IEC 61076-2-101

**General data**

Number of poles	12	Coding	A-coded
Connection thread	M12	Contact surface	Gold-plated
Type of connection	Pin	Housing main material	Zinc diecast
Nominal voltage	30 V	Nominal current	2 A
Protection degree	IP67, when fully mounted	Cable gland	PG 9
Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)
Connection 1	M12	Connection 2	Dip soldering
Temperature range of housing	-40 ... +85 ° C		
		Conductor O.D.	-

**Classifications**

ETIM 8.0	EC003568	ETIM 9.0	EC003568
ETIM 10.0	EC003568	ECLASS 14.0	27-44-01-10
ECLASS 15.0	27-44-01-10		

**SAIE-M12S-12S-TL-HW-PG9**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Pole scheme**

