

POWER MONITOR 51A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Energy meters - ValueLine**

Advanced functionality of energy data capture

The scope of performance of the ValueLine energy meters goes beyond the core functions of energy measurement.

They are also suitable for determining, storing and visualising further energy quality parameters.

The free "ecoExplorer go" software is available for most types of the product group,

on the one hand for device configuration / commissioning / visualisation of the measured values and on the other hand for analysing the power quality.

General ordering data

Version	Power measurement/display for 1-, 3-phase mains
Order No.	1470260000
Type	POWER MONITOR 51A
GTIN (EAN)	4050118276756
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-12-30T00:00:00+01:00

POWER MONITOR 51A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	68 mm	Depth (inches)	2.6772 inch
Height	96 mm	Height (inches)	3.7795 inch
Width	96 mm	Width (inches)	3.7795 inch
Net weight	386 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-25 °C...55 °C
Humidity	35 % to 85 % relative humidity level		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Measuring current input

Rated current	1 / 5 A	Current-measuring channels	4
Measuring accuracy for current	0.5 %	Residual current measuring	No

Measuring voltage input

Measuring accuracy for voltage	0.5 %	Three-wire system	Yes
Measurement range, voltage L-L, AC	0...500 V	Measurement range, voltage L-N, AC	0...250 V (1P3W), 0...289 V (3P4W)
Four-wire system	Yes		

Communication

Interface	RS485: Autobaud, 9,6 – 115.2 kbps (pluggable screw terminals), USB	Protocol	Modbus RTU
-----------	--	----------	------------

Inputs/outputs

Number of digital inputs	2	Number of digital outputs	2
--------------------------	---	---------------------------	---

Measurement data recording

Memory; minimum and maximum values	No	Software	Power Monitor Manager
Integrated logic	No		

POWER MONITOR 51A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technical data

Display value	Apparent power, Effective power, Reactive power, Power factor, Voltage, Current, Frequency, Temperature, Voltage unbalance, Current unbalance, THD-I, THD-U, Voltage harmonic, Current harmonic	Version	Power measurement/display for 1-, 3-phase mains
Protection degree	Front panel: IP5 1, Enclosure: IP20	Pollution severity	2
Rated current	1 / 5 A	Standards	IEC 61010-1
Measurement range, voltage L-N, AC	0...250 V (1P3W), 0...289 V (3P4W)	Measurement range, voltage L-L, AC	0...500 V
Surge voltage category	II	Supply voltage	85...264 VAC, 100...300 V DC
Supply voltage	230 V	Three-wire system	Yes
Four-wire system	Yes	Sampling frequency 50/60 Hz	1024 kHz
Measurement result per second	100000 ms	Residual current measuring	No
Current-measuring channels	4	Measuring accuracy for voltage	0.5 %
Measuring accuracy for current	0.5 %	Measurement accuracy for active energy (kWh, .../5 A)	1% for the calculated values
Operating-hours counter	No	Clock	Yes

Voltage quality measurement

Unbalanced	Yes	Positive, negative and zero system	Yes
Brief interruptions	Yes	Sequence-of-events recorder function	No

Insulation coordination

Surge voltage category	II	Pollution severity	2
------------------------	----	--------------------	---

Classifications

ETIM 8.0	EC002301	ETIM 9.0	EC002301
ETIM 10.0	EC002301	ECLASS 14.0	27-14-23-30
ECLASS 15.0	27-14-23-30		

Tender specification sheets

Long specification	Electrical parameters have to be measured and visualised to optimise your machines' and systems' energy requirements. Only this allows analysis and, subsequently, the achievement of savings and the establishment of an energy management system. An easy-to-install solution is now available from Weidmüller. When implementing an energy management system according to ISO 50001, the Power Monitor 51A is one of the modules necessary to meet the	Short specification	Measuring device with memory function for optimising energy requirements
--------------------	---	---------------------	--

POWER MONITOR 51A**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data**

requirements of recording,
displaying and analysing
power flows.

Technical data:

Input data: measurement
variable: active, reactive,
apparent power

Recording of frequencies
up to 99.99 Hz and
temperatures up to 100°C

Measurement variable:
AC sine (50/60 Hz)
designation

Input: voltage
measurement inputs V1,
V2, V3

Input voltage range: 0 V
AC ... 500 V AC (phase/
phase)

Input voltage range: 0 V
AC ... 300 V AC (phase/
neutral conductor)

Accuracy: 0.5% input
current range: via external
converters, input current:
8,000 A (primary), input
current: 5 A (secondary) ,
Response threshold of
rated measurement range
value: 1 mA

Power-measurement
range: 0 kW ... 9999999.9
kW

Power-measurement
range: 0 kvar ...
9999999.9 kvar

Power-measurement
range: 0 kVA ...
9999999.9 kVA

Up to 31 harmonics.

Accuracy: 1%
Interface: RS-485

Type of connection: screw
terminals

General data: width: 96
mm, height: 96 mm

Display: LCD with backlit
display

Supply voltage range: 85 V
AC ... 264 V AC

Rated power
consumption: 6 VA,
protection degree: IP51
(front), IP20 (rear):

Type of mains network: 3-
phase (3- or 4-conductor),
2-phase (2-conductor) and
1-phase (1-conductor) also
able to measure current in
the neutral conductor

Colour: black; conformity:
CE marking

Rated insulation voltage:
300 V AC (EN 61010-1)

Overvoltage category:
II, ambient temperature
(operational): -25°C ...

55°C, ambient temperature

POWER MONITOR 51A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

(storage/transport):
-25°C ... 70°C
Max. perm. humidity
(operation): 85%, height
ASL <2000 m
Connection data: flexible
conductor cross-section
min.: 0.5 mm², flexible
conductor cross-section
max.: 2.5 mm², rigid
conductor cross-section
min.: 0.2 mm², rigid
conductor cross-section
max.: 4 mm², type of
connection: screw
connection
Ordering details: product:
Weidmüller Interface, type:
Power Monitor, item no.:
1470260000

POWER MONITOR 51A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Measurements Items


Item	Unit	Data display range
Instantaneous power	Active kW	-99999 to 99999
	Reactive kvar	
	Apparent kVA	
Integral power (import)	Active kWh	0.000 to 9999999.9
	Reactive kvarh	
	Apparent kVAh	
Integral power for each time zone (4-zone) (import)	Active kWh	0.000 to 9999999.9
	Reactive kvarh	
	Apparent kVAh	
Integral power for each time zone (4-zone) (export)	Active kWh	0.000 to 9999999.9
	Reactive kvarh	
Current	A	0.000 to 99999
Voltage	V	0.000 to 99999
Power factor		-1.000 to 1.000
Frequency	Hz	0.00 to 99.99
Pulse count value		0.000 to 9999999.9
Pulse conversion value		0.000 to 9999999.9
Temperature	°C	-100.0 to 100.0
Calendar		January 1, 2000 00:00:00 - December 31, 2099 23:59:59

POWER MONITOR 51A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****General ordering data**

Type	POWER MONITOR BRACKET	Version	
Order No.	2091060000		
GTIN (EAN)	4050118421903		
Qty.	1 ST		