

SAISWC-M-4D-5/8-M12-CF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability. Crimp contacts are to be ordered separately.

General ordering data

| | |
|------------|---------------------------------|
| Version | Field attachable connector, M12 |
| Order No. | 1467850000 |
| Type | SAISWC-M-4D-5/8-M12-CF |
| GTIN (EAN) | 4050118273632 |
| Qty. | 1 items |

SAISWC-M-4D-5/8-M12-CF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 60.5 g

Environmental Product Compliance

RoHS Compliance Status Compliant
REACH SVHC Lead 7439-92-1
SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

| | | | |
|--------------------------------|----------------------|--------------------------------|----------------------|
| Number of poles | 4 | Coding | D-coded |
| Contact surface | Gold-plated | Type of connection | Crimp connection |
| Housing main material | CuZn | Cable diameter, max. | 8 mm |
| Cable diameter, min. | 5 mm | Conductor cross-section, max. | 0.5 mm ² |
| Conductor cross-section, min. | 0.34 mm ² | Nominal voltage | 250 V |
| Nominal current | 4 A | Protection degree | IP67 |
| Plugging cycles | ≥ 200 | Pollution severity | 3 |
| Gender of contact | Male | Shield connection | Yes |
| Threaded ring material | Diecast zinc | Temperature range of housing | -40 ... +85 ° C |
| Connection cross-section, max. | 0.5 mm ² | Connection cross-section, min. | 0.34 mm ² |

General Info

| | | | |
|-------------------|-------|-----------------------|-------------|
| Number of poles | 4 | Connection 1 | M12 |
| Connection 2 | Crimp | Housing main material | CuZn |
| Connection thread | M12 | Contact surface | Gold-plated |
| Protection degree | IP67 | Plugging cycles | ≥ 200 |

Electrical properties

Nominal voltage 250 V

General standards

Connector standard IEC 61076-2-101

Standards

Connector standard IEC 61076-2-101

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ETIM 10.0 | EC002635 | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 | | |

Pole scheme

