

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	1476920000
Type	CA 100 - 2.5
GTIN (EAN)	4050118283754
Qty.	1 items

CA 100 - 2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	420 mm	Depth (inches)	16.5354 inch
Height	425 mm	Height (inches)	16.7323 inch
Width	470 mm	Width (inches)	18.5039 inch
Net weight	38000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Stripping range	0.34 - 4 mm ² (~AWG 22 - 12)	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Crimping	Quadrocrimp
Wire end ferrules cross-section, max.	4 mm ²	Wire end ferrules cross-section, min.	0.34 mm ²
Crimping length	6/8/10/12 mm	Consumables	loose cable lugs, with plastic collar
Length of wire-end ferrule	12/14/16/18 mm	Compressed-air connection	5 bar
Electrical connection	100-240 V / 50/65 Hz		

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

Drawings

