

LPA QB 24




Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image





Similar to illustration

Large potential for small terminals.

For efficient electrical distribution directly at the connection:


- Isolated comb rail
- Available with the most standard pole numbers
- Easy to shorten

Simply reduce in size to match the number of poles and connect with the conductor in a single working procedure.

For retrofitting or deliberate reduction of the thermal load on the PCB.

General ordering data

Printed circuit board terminals, Accessories, Cross-connector, Number of poles: 24	
<u>1472600000</u>	
LPA QB 24	
4008190102203	
20 items	
Вох	



LPA QB 24



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals				
ROHS	Conform			
Dimensions and weights				
Vet weight	6.5 g			
Environmental Product Comp				
RoHS Compliance Status REACH SVHC	Compliant without exemption No SVHC above 0.1 wt%	on		
	No Syric above 0.1 Wt%			
System parameters				
Pitch in mm (P)	5.08 mm	Pitch in inches (P)	0.200 "	
Number of poles	24	Pin series quantity	1	
_1 in inches	0.200 "	Protection degree	IP20	
Vlaterial data				
Contact material	Cu-alloy	Storage temperature, min.	-40 °C	
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C	
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C	
Temperature range, installation, max.	100 °C			
Conductors suitable for conn	ection			
Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)			
Rated data acc. to IEC				
ested acc. to standard	IEC 60664-1, IEC 61984			
Packing				
Packaging /PE width	Box 120.00 mm	VPE length	168.00 mm 39.00 mm	
	120.00 mm	VPE height	39.00 mm	
mportant note				
PC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the product can be evaluated on request.			
Notes	 Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months 			
Classifications		,		
ETIM 6.0	EC002848	ETIM 7.0	EC002848	
ETIM 8.0	EC002848	ETIM 9.0	EC002848	

Creation date 29.11.2025 08:39:23 MEZ

Catalogue status / Drawings 2



LPA QB 24



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

ETIM 10.0	EC002848	ECLASS 9.0	27-44-04-92
ECLASS 9.1	27-44-04-92	ECLASS 10.0	27-44-04-92
ECLASS 11.0	27-46-04-06	ECLASS 12.0	27-46-04-06
ECLASS 13.0	27-46-04-06	ECLASS 14.0	27-46-04-06
ECLASS 15.0	27-46-04-06		