


#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**

























The innovative quick connector - simple, safe and economical:

PCB terminals with spring connection and direct PUSH IN technology. A milestone in connection technology.

Amazingly simple and simply amazing in practice:

- Connect and easily detach solid wires or wires with wire-end ferrules without using tools
- Processed automatically in the reflow or vapour phase
- Potentials and clamping points marked clearly by coloured push buttons

World-class design-in and processing phases, and suitable for a vast range of applications.

PCB terminal for fully automatic assembly using reflow soldering (SMD), with PUSH IN wire connections. Conductor insertion and slider operation from the same direction (TOP).

- Solid & flexible conductors with wire-end ferrules need only to be inserted and they are ready.
- When connecting stranded wires without wire-end ferrules the actuating element is used to open the terminal point
- Intuitive handling since the wire-entry area and handling area are clearly separated.
- Packaged in tape-on-reel
- Conductor outlet direction 135°

#### **General ordering data**

| Version      | Printed circuit board terminals, 3.50 mm, Number of poles: 9, 135°, black, PUSH IN with actuator, Clamping range, max.: 1.5 mm², Tape |
|--------------|---|
| Order No.    | <u>1473390000</u>   |
| Туре         | LSF-SMD 3.50/09/135 SN BK RL  |
| GTIN (EAN)   | 4050118279818   |
| Qty.         | 210 items   |
| Product data | IEC: 320 V / 12 A / 0.2 - 1.5 mm²<br>UL: 300 V / 12 A / AWG 28 - AWG 14   |
| Packaging    | Таре  |
|              |   |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

## **Approvals**

Approvals



| ROHS                    | Conform           |  |
|-------------------------|-------------------|--|
| UL File Number Search   | <u>UL Website</u> |  |
| Certificate No. (cURus) | F60693            |  |

### **Dimensions and weights**

| Depth                    | 12.7 mm     | Depth (inches)  | 0.5 inch    |
|--------------------------|-------------|-----------------|-------------|
| Height                   | 14.45 mm    | Height (inches) | 0.5689 inch |
| Height of lowest version | 14.45 mm    | Width           | 32.2 mm     |
| Width (inches)           | 1.2677 inch | Net weight      | 7.87 g      |

#### **Temperatures**

Continuous operating temp., max. 120 °C

### **Environmental Product Compliance**

| RoHS Compliance Status | Compliant without exemption |
|------------------------|-----------------------------|
| REACH SVHC             | No SVHC above 0.1 wt%       |

### **System parameters**

| Product family                               | OMNIMATE Signal - series<br>LSF | Wire connection method                     | PUSH IN with actuator |
|--|---------------------------------|--|-----------------------|
| Mounting onto the PCB                        | SMD solder connection           | Conductor outlet direction                 | 135°                  |
| Pitch in mm (P)                              | 3.50 mm                         | Pitch in inches (P)                        | 0.138 "               |
| Number of poles                              | 9                               | Pin series quantity                        | 1                     |
| Fitted by customer                           | No                              | Number of rows                             | 1                     |
| Coplanarity:                                 | 100 μm                          | Number of solder pins per pole             | 2                     |
| Stripping length                             | 8 mm                            | L1 in mm                                   | 28.00 mm              |
| L1 in inches                                 | 1.104 "                         | Touch-safe protection acc. to DIN VDE 0470 | IP 20                 |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch          | Protection degree                          | IP20                  |
| Volume resistance                            | 1.60 mΩ                         |  |                       |

#### **Material data**

| Insulating material                   | LCP GF        | Colour                                | black    |
|---------------------------------------|---------------|---------------------------------------|----------|
| Colour chart (similar)                | RAL 9011      | Insulating material group             | Illa     |
| Comparative Tracking Index (CTI)      | ≥ 175         | Moisture Level (MSL)                  | 1        |
| UL 94 flammability rating             | V-0           | Contact material                      | Cu-alloy |
| Layer structure of solder connection  | 46 µm Sn matt | Storage temperature, min.             | -40 °C   |
| Storage temperature, max.             | 70 °C         | Operating temperature, min.           | -50 °C   |
| Operating temperature, max.           | 120 °C        | Temperature range, installation, min. | -30 °C   |
| Temperature range, installation, max. | 120 °C        |                                       |          |

### **Conductors suitable for connection**

| Clamping range, min. | 0.13 mm <sup>2</sup> |  |
|----------------------|----------------------|--|
| Clamping range, max. | 1.5 mm <sup>2</sup>  |  |

Creation date 29.11.2025 06:26:33 MEZ







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| Wire connection cross section AWG,             | AWG 28  |                                  |                         |
|--|---|----------------------------------|-------------------------|
| min.   |   |                                  |                         |
| Wire connection cross section AWG, max.        | AWG 14  |                                  |                         |
| Solid, min. H05(07) V-U                        | 0.2 mm <sup>2</sup>   |                                  |                         |
| Solid, max. H05(07) V-U                        | 1.5 mm <sup>2</sup>   |                                  |                         |
| Flexible, min. H05(07) V-K                     | 0.2 mm <sup>2</sup>   |                                  |                         |
| Flexible, max. H05(07) V-K                     | 1.5 mm <sup>2</sup>   |                                  |                         |
| w. plastic collar ferrule, DIN 46228 pt 4 min. | 4, 0.25 mm²   |                                  |                         |
| w. plastic collar ferrule, DIN 46228 pt 4 max. | 4, 0.75 mm <sup>2</sup>   |                                  |                         |
| w. wire end ferrule, DIN 46228 pt 1, min.      | 0.25 mm <sup>2</sup>  |                                  |                         |
| w. wire end ferrule, DIN 46228 pt 1, max.      | 1.5 mm <sup>2</sup>   |                                  |                         |
| Clampable conductor                            | Cross-section for conductor connection  | Туре                             | fine-wired              |
|  |   | nominal                          | 0.25 mm <sup>2</sup>    |
|  | wire end ferrule  | Stripping length                 | nominal 10 mm           |
|  |   | Recommended wire-<br>end ferrule | H0,25/12 HBL            |
|  | Cross-section for conductor connection  | Туре                             | fine-wired              |
|  |   | nominal                          | 0.34 mm <sup>2</sup>    |
|  | wire end ferrule  | Stripping length                 | nominal 10 mm           |
|  |   | Recommended wire-<br>end ferrule | H0,34/12 TK             |
|  | Cross-section for conductor connection  | Туре                             | fine-wired              |
|  |   | nominal                          | 0.5 mm <sup>2</sup>     |
|  | wire end ferrule  | Stripping length                 | nominal 10 mm           |
|  |   | Recommended wire-<br>end ferrule | H0.5/14 OR              |
|  | Cross-section for conductor connection  | Туре                             | fine-wired              |
|  |   | nominal                          | 0.75 mm <sup>2</sup>    |
|  | wire end ferrule  | Stripping length                 | nominal 10 mm           |
|  |   | Recommended wire-<br>end ferrule | H0,75/14T HBL           |
| Reference text                                 | Length of ferrules is to be chosen depending or diameter of the plastic collar should not be larg |                                  | d voltage., The outside |

Rated data acc. to IEC

| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 12 A             |
|---|------------------------|---|------------------|
| Rated current, max. number of poles (Tu=20°C)                             | 12 A                   | Rated current, min. number of poles (Tu=40°C)                         | 12 A             |
| Rated current, max. number of poles (Tu=40°C)                             | 12 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 80 A |

# Rated data acc. to CSA

| Institute (CSA)                   | CSA    | Certificate No. (CSA)             | 200039-1664286 |
|-----------------------------------|--------|-----------------------------------|----------------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 10 A   | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 28 | Wire cross-section, AWG, max.     | AWG 14         |

Creation date 29.11.2025 06:26:33 MEZ





### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| Reference to approval values | Specifications are        |
|------------------------------|---------------------------|
|                              | maximum values, details - |
|                              | see approval certificate. |

## Rated data acc. to UL 1059

| Institute (cURus)                     | CURUS  | Certificate No. (cURus)               | E60693 |
|---------------------------------------|--|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 12 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 28   | Wire cross-section, AWG, max.         | AWG 14 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

### **Packing**

| ESD Level packaging         | static dissipative | Packaging                | Tape      |
|-----------------------------|--------------------|--------------------------|-----------|
| VPE length                  | 330.00 mm          | VPE width                | 330.00 mm |
| VPE height                  | 60.00 mm           | Tape depth (T2)          | 15.70 mm  |
| Tape width (W)              | 56 mm              | Tape pocket depth (K0)   | 15.20 mm  |
| Tape pocket height (A0)     | 11.30 mm           | Tape pocket width (B0)   | 44.06 mm  |
| Tape pocket separation (P1) | 20.00 mm           | Tape hole separation (E) | 1.75 mm   |
| Tape pocket separation (F)  | 26.20 mm           | Tape reel diameter Ø (A) | 330 mm    |
| Surface resistance          | Rs = 109 - 1012 Ω  |                          |           |

## Type tests

| Test: Durability of markings      | Test           | mark of origin, type identification, pitch, approval                               |  |  |
|-----------------------------------|----------------|--|--|--|
| ,                                 |                | marking UL, durability   |  |  |
| Test: Clampable cross section     | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |  |  |
|                                   | Conductor type | Type of conductor solid 0.14 mm <sup>2</sup> and conductor cross-section           |  |  |
|                                   |                | Type of conductor stranded 0.14 mm <sup>2</sup> and conductor cross-section        |  |  |
|                                   |                | Type of conductor solid 1.5 mm <sup>2</sup> and conductor cross-section            |  |  |
|                                   |                | Type of conductor stranded 1.5 mm <sup>2</sup> and conductor cross-section         |  |  |
|                                   |                | Type of conductor AWG 24/1 and conductor cross-section                             |  |  |
|                                   |                | Type of conductor AWG 22/19 and conductor cross-section                            |  |  |
|                                   |                | Type of conductor AWG 16/1 and conductor cross-section                             |  |  |
|                                   |                | Type of conductor AWG 16/19 and conductor cross-section                            |  |  |
|                                   | Evaluation     | passed   |  |  |
| Test for damage to and accidental | Standard       | DIN EN 60999-1 section 9.4 / 12.00   |  |  |
| loosening of conductors           | Requirement    | 0.2 kg   |  |  |
|                                   | Conductor type | Type of conductor AWG 24/1 and conductor cross-section                             |  |  |

Creation date 29.11.2025 06:26:33 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

|   |                   | Type of conductor and conductor cross-section | AWG 24/19                     |  |
|---|-------------------|---|-------------------------------|--|
|   | Evaluation        | passed  |                               |  |
|   | Requirement       | 0.3 kg  |                               |  |
|   | Conductor type    | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |  |
|   |                   | Type of conductor and conductor cross-section | solid 0.5 mm²                 |  |
|   | Evaluation        | passed  |                               |  |
|   | Requirement       | 0.4 kg  |                               |  |
|   | Conductor type    | Type of conductor and conductor cross-section | solid 1.5 mm²                 |  |
|   |                   | Type of conductor and conductor cross-section | stranded 1.5 mm <sup>2</sup>  |  |
|   |                   | Type of conductor and conductor cross-section | AWG 16/1                      |  |
|   |                   | Type of conductor and conductor cross-section | AWG 16/19                     |  |
|   | Evaluation        | passed  |                               |  |
|   | Standard          | DIN EN 60999-1 section                        | n 9.5 / 12.00                 |  |
|   | Requirement       | ≥10 N   |                               |  |
|   | Conductor type    | Type of conductor and conductor cross-section | AWG 24/1                      |  |
|   |                   | Type of conductor and conductor cross-section | AWG 24/19                     |  |
|   | valuation passed  |   |                               |  |
|   | Requirement       | ≥20 N   |                               |  |
| C | Conductor type    | Type of conductor and conductor cross-section | stranded 0.25 mm <sup>2</sup> |  |
|   |                   | Type of conductor and conductor cross-section | H05V-U0.5                     |  |
|   | Evaluation passed |   |                               |  |
|   | Requirement       | ≥40 N   |                               |  |
|   | Conductor type    | Type of conductor and conductor cross-section | H07V-U1.5                     |  |
|   |                   | Type of conductor and conductor cross-section | H07V-K1.5                     |  |
|   |                   | Type of conductor and conductor cross-section | AWG 16/1                      |  |
|   |                   | Type of conductor and conductor cross-section | AWG 16/19                     |  |
|   | Evaluation        | passed  |                               |  |

#### Important note

IPC conformity

Pull-out test

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp.







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

- Additional push button colours on request
- Operating force of slider max. 40 N
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule with plastic collar to DIN 46228/4
- Wire end ferrule without plastic collar to DIN 46228/1
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

#### Classifications

| ETIM 6.0    | EC002643    | ETIM 7.0    | EC002643    |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 9.0  | 27-44-04-01 |
| ECLASS 9.1  | 27-44-04-01 | ECLASS 10.0 | 27-44-04-01 |
| ECLASS 11.0 | 27-46-01-01 | ECLASS 12.0 | 27-46-01-01 |
| ECLASS 13.0 | 27-46-01-01 | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |
|             |             |             |             |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**


# **Product image**




# **Dimensional drawing**



### Graph




### **Product benefits**



Stable solder connection

### **Product benefits**



PUSH IN wire connection



Weidmüller Interface GmbH & Co. KG

8

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com


# **Drawings**

### **Product benefits**




Packaged in tape-on-reel

# **Dimensional drawing**



### **Dimensional drawing**



DIRECTION OF UNREELING