

CC-M 27/18 ST SDR**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	MetalliCard, Device markers, 26.8 x 18 mm, silver
Order No.	1474120000
Type	CC-M 27/18 ST SDR
GTIN (EAN)	4050118290356
Qty.	1 items

CC-M 27/18 ST SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	26.8 mm	Height (inches)	1.0551 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	1.84 g		

Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	pluggable	
Width	18 mm	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Colour	silver	
Basic material	Stainless steel 1.4301	
Printed characters	Requires M-Print PRO File	
Number of markers per packaging unit	Form of supply	MetalliCard
Size of labelling field	25 x 15 mm	
compatible printer		
Number of markers per combination	1 MetalliCard = Device markers	
Operating temperature range	-55...130 °C	

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings

Example of use

