


**CC-M 58/35 2X3 ST SDR****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 58 x 34.8 mm, silver
Order No.	<a href="#">1474360000</a>
Type	CC-M 58/35 2X3 ST SDR
GTIN (EAN)	4050118290776
Qty.	1 items

## CC-M 58/35 2X3 ST SDR

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	34.8 mm	Width (inches)	1.3701 inch
Net weight	17.4 g		

## Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Version	pluggable, with 3.5 mm mounting hole				
Width	34.8 mm				
Operating temperature range, max.	130 °C				
Operating temperature range, min.	-55 °C				
Colour	silver				
Basic material	Micro-etched stainless steel 1.4301 (ST), Stainless steel 1.4301				
Printed characters	Requires M-Print PRO File				
Number of markers per packaging unit	Form of supply	MetalliCard			
Size of labelling field	56 x 33 mm				
compatible printer					
Number of markers per combination	1 MetalliCard = Device markers				
Operating temperature range	-55...130 °C				

## Device markers

Drill-hole diameter	3.40 mm
---------------------	---------

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

## CC-M 58/35 2X3 ST SDR

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use

