Data sheet

# SAISWS-K-4A-6/8-M12

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.
Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.
The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

## General ordering data

| | |
|---|---|
| Version | Field attachable connector, M12 |
| Order No. | 1481150000 |
| Type | SAISWS-K-4A-6/8-M12 |
| GTIN (EAN) | 4050118289695 |
| Qty. | 1 items |

# Data sheet

## SAISWS-K-4A-6/8-M12

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 17 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | ebf89fc8-a87f-4691-b87a-dfb9921774b4 |

### Technical data customisable plug-in connectors

| | | | |
|---|---|---|---|
| Number of poles | 4 | Coding | A-coded |
| Contact surface | CuSnZn | Type of connection | Screw connection |
| Housing main material | PA | Insulation resistance | 108 Ω |
| Cable diameter, max. | 8 mm | Cable diameter, min. | 6 mm |
| Conductor cross-section, max. | 0.75 mm² | Conductor cross-section, min. | 0.14 mm² |
| Nominal voltage | 250 V | Nominal current | 4 A |
| Protection degree | IP67 | Plugging cycles | ≥ 50 |
| Pollution severity | 3 | Gender of contact | Male |
| Shield connection | No | Threaded ring material | Plastic |
| Temperature range of housing | -40 … +85 ° C | | |

### General Info

| | | | |
|---|---|---|---|
| Number of poles | 4 | Connection 1 | M12 |
| Connection 2 | Screw | Housing main material | PA |
| Connection thread | M12 | Contact surface | CuSnZn |
| Protection degree | IP67 | Plugging cycles | ≥ 50 |

### Standards

| | |
|---|---|
| Connector standard | IEC 61076-2-101 |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC002635 | ETIM 9.0 | EC002635 |
| ETIM 10.0 | EC002635 | ECLASS 14.0 | 27-44-01-16 |
| ECLASS 15.0 | 27-44-01-16 | | |

# SAISWS-K-4A-6/8-M12

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

### Pole scheme

