

CC-M 10/30 2X2.5 AL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | MetalliCard, Device markers, 10 x 30 mm, silver |
| Order No. | 1483780000 |
| Type | CC-M 10/30 2X2.5 AL |
| GTIN (EAN) | 4050118292862 |
| Qty. | 200 items |

CC-M 10/30 2X2.5 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.5 mm | Depth (inches) | 0.0197 inch |
| Height | 10 mm | Height (inches) | 0.3937 inch |
| Width | 30 mm | Width (inches) | 1.1811 inch |
| Net weight | 0.4 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...130 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--------------------------------------|--------------------------------|-------------|--|
| Width | 30 mm | | |
| Operating temperature range, max. | 130 °C | | |
| Operating temperature range, min. | -55 °C | | |
| Colour | silver | | |
| Basic material | Anodized aluminium | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | MetalliCard | |
| Size of labelling field | 10.2 x 22.5 mm | | |
| Recommended industries | Energy, Process | | |
| compatible printer | | | |
| Number of markers per combination | 1 MetalliCard = Device markers | | |
| Operating temperature range | -55...130 °C | | |

Device markers

| | |
|---------------------|---------|
| Drill-hole diameter | 2.50 mm |
|---------------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Example of use



CC-M 10/30 2X2.5 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Complementary products



General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | INLAY CC-M 10/30 | Version | |
| Order No. | 1483770000 | | |
| GTIN (EAN) | 4050118293081 | | |
| Qty. | 1 ST | | |
| Type | PRIMER CC-M | Version | |
| Order No. | 2068020000 | | |
| GTIN (EAN) | 4050118416534 | | |
| Qty. | 100 ST | | |