

HDC HP550 CP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Accessories especially suitable for the demands of wagon-to-wagon coupling have been developed for the HighPower end-wall connectors and thus significantly enhance the added value of the plug-in connectors. Easy-to-install coding pins ensure reverse polarity protection, plastic cover caps provide sufficient dust protection, while aluminium covers are designed to be absolutely water and dust-proof. The accessories intelligently round off the overall system.

General ordering data

Version	HDC enclosures, 0 V, Number of poles: 0, Screw connection, Installation size: Miscellaneous
Order No.	1475840000
Type	HDC HP550 CP
GTIN (EAN)	4050118282511
Qty.	200 items

HDC HP550 CP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	5 mm	Height (inches)	0.1968 inch
Width	5 mm	Width (inches)	0.1968 inch
Diameter	5 mm	Net weight	1.86 g

Temperatures

Limit temperature	-40 °C ... 120 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Dimensions

Width	5 mm
-------	------

General data

Number of poles	0	Type of connection	Screw connection
Installation size	Miscellaneous	UL 94 flammability rating	V-0
Colour	silver	Surface finish	galvanized
Basic material	Steel, galvanised	Rated voltage (DIN EN 61984)	0 V
Free from halogens	false	EMC housings	No
BG	Miscellaneous	Protection degree	None

General data

Type of connection	Screw connection	Colour	silver
Conductor cross-section, max.	0 mm ²	Surface finish	galvanized
Basic material	Steel, galvanised		

Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		