

**HDC HP550 CP****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Accessories especially suitable for the demands of wagon-to-wagon coupling have been developed for the HighPower end-wall connectors and thus significantly enhance the added value of the plug-in connectors. Easy-to-install coding pins ensure reverse polarity protection, plastic cover caps provide sufficient dust protection, while aluminium covers are designed to be absolutely water and dust-proof. The accessories intelligently round off the overall system.

**General ordering data**

Version	HDC enclosures, Installation size: Miscellaneous
Order No.	<a href="#">1475840000</a>
Type	HDC HP550 CP
GTIN (EAN)	4050118282511
Qty.	200 items

## HDC HP550 CP

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	5 mm	Height (inches)	0.1968 inch
Width	5 mm	Width (inches)	0.1968 inch
Diameter	5 mm	Net weight	1.86 g

## Temperatures

Limit temperature	-40 °C ... 120 °C
-------------------	-------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

## Dimensions

Width	5 mm
-------	------

## General data

Installation size	Miscellaneous	UL 94 flammability rating	V-0
Colour	silver	Surface finish	galvanized
Basic material	Steel, galvanised	Free from halogens	false
BG	Miscellaneous		

## General data

Colour	silver	Surface finish	galvanized
Basic material	Steel, galvanised		

## Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

## Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		