

HSS 8.5-25.4 EL W10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 8.5 - 25.4 mm, white |
| Order No. | 1489690000 |
| Type | HSS 8.5-25.4 EL W10M |
| GTIN (EAN) | 4050118299434 |
| Qty. | 1 items |

HSS 8.5-25.4 EL W10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E366310 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Width | 40.5 mm | Width (inches) | 1.5945 inch |
| Length | 10000 mm | Length (inches) | 393.7 inch |
| Net weight | 416 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|--|-----------------------------------|---|
| Type of printing | neutral | Width | 40.5 mm |
| Operating temperature range, max. | 135 °C | Operating temperature range, min. | -55 °C |
| Colour | white | Halogen | Yes |
| Length | 10000 mm | Basic material | Polyolefine |
| Printed characters | without | Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | Operating temperature range | -55...135 °C |

Conductor and cable markers

| | | | |
|-----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 120 mm ² |
| Conductor cross-section, min. | 35 mm ² | Conductor O.D., max. | 25.4 mm |
| Conductor O.D., min. | 8.5 mm | Rate of shrinkage | 3:1 |
| Recommended shrinking temperature | 90 °C | Text field width | 0 mm |
| Text field height | 40.3 mm | Conductor O.D. | 8.5 - 25.4 mm |
| Cross-section for connected wire | 35 - 120 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

HSS 8.5-25.4 EL W10M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON HSS HF EL 40/300... | Version | |
| Order No. | 1426210000 | Ink ribbon | |
| GTIN (EAN) | 4050118228823 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |
| Type | MULTIMARK ROLLER 30 | Version | |
| Order No. | 1357430000 | | |
| GTIN (EAN) | 4050118160253 | | |
| Qty. | 1 ST | | |