

**KQNG-M6/-16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|                 |                                                                  |
|-----------------|------------------------------------------------------------------|
| Version         | cable lug, terminal end, 16 mm <sup>2</sup> , 16 mm <sup>2</sup> |
| Order No.       | <a href="#">1492700000</a>                                       |
| Type            | KQNG-M6/-16                                                      |
| GTIN (EAN)      | 4050118302493                                                    |
| Qty.            | 50 items                                                         |
| Delivery status | This article will no longer be available in the future.          |
| Last order date | 2026-03-31T00:00:00+02:00                                        |

**KQNG-M6/-16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 4.78 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Connectors**

|                                |                    |                                |                    |
|--------------------------------|--------------------|--------------------------------|--------------------|
| Conductor cross-section, max.  | 16 mm <sup>2</sup> | Conductor cross-section        | 16 mm <sup>2</sup> |
| Insulation                     | not available      | Hole                           | C 6                |
| Inside diameter of shaft (d1)  | 5.8 mm             | Outside diameter of shaft (d3) | 11 mm              |
| Shaft length (a)               | 10 mm              | Connection length (l)          | 20 mm              |
| Inside diameter of flange (d2) | 6.5 mm             |                                |                    |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001059    | ETIM 9.0    | EC001059    |
| ETIM 10.0   | EC001059    | ECLASS 14.0 | 27-40-02-92 |
| ECLASS 15.0 | 27-40-02-92 |             |             |

**Drawings**

