

## KRN-M6/-1,5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

Version	cable lug, terminal end, 1,5 mm <sup>2</sup> , 1 mm <sup>2</sup> - 1,5 mm <sup>2</sup>
Order No.	<a href="#">1495080000</a>
Type	KRN-M6/-1,5
GTIN (EAN)	4050118304732
Qty.	100 items

## KRN-M6/-1,5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	1.7 g
------------	-------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Version	Euro series, standard
---------	-----------------------

### Connectors

Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	1 mm <sup>2</sup>
Conductor cross-section	1.5 mm <sup>2</sup>	Insulation	not available
Hole	M 6	Identification colour	None
Inside diameter of shaft (d1)	1.9 mm	Outside diameter of shaft (d3)	3.9 mm
Shaft length (a)	6 mm	Connection length (l)	18 mm
Inside diameter of flange (d2)	6.4 mm	Flange width (b)	11 mm

### Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

**Drawings**

