

## KRN-M12/-240

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

Version	cable lug, terminal end, 240 mm <sup>2</sup> , 240 mm <sup>2</sup> - 240 mm <sup>2</sup>
Order No.	<a href="#">1495500000</a>
Type	KRN-M12/-240
GTIN (EAN)	4050118305142
Qty.	25 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Net weight	129.84 g
------------	----------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Version	Euro series, standard
---------	-----------------------

**Connectors**

Conductor cross-section, max.	240 mm <sup>2</sup>	Conductor cross-section, min.	240 mm <sup>2</sup>
Conductor cross-section	240 mm <sup>2</sup>	Insulation	not available
Hole	M 12	Identification colour	None
Inside diameter of shaft (d1)	21 mm	Outside diameter of shaft (d3)	26 mm
Shaft length (a)	35 mm	Connection length (l)	67 mm
Inside diameter of flange (d2)	13 mm	Flange width (b)	38 mm

**Classifications**

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

Drawings

