



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

Version	cable lug, terminal end, 120 mm <sup>2</sup> , 120 mm <sup>2</sup> - 120 mm <sup>2</sup>
Order No.	<a href="#">1495790000</a>
Type	KRN-M8/-120
GTIN (EAN)	4050118305401
Qty.	25 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	68.8 g
------------	--------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical data

Version	Euro series, standard
---------	-----------------------

### Connectors

Conductor cross-section, max.	120 mm <sup>2</sup>	Conductor cross-section, min.	120 mm <sup>2</sup>
Conductor cross-section	120 mm <sup>2</sup>	Insulation	not available
Hole	M8	Identification colour	None
Inside diameter of shaft (d1)	15 mm	Outside diameter of shaft (d3)	20 mm
Shaft length (a)	26 mm	Connection length (l)	49.5 mm
Inside diameter of flange (d2)	8.4 mm	Flange width (b)	29 mm

### Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

Drawings

