

KWPN-M20/-185 90**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end, 185 mm ²
Order No.	1496720000
Type	KWPN-M20/-185 90
GTIN (EAN)	4050118306187
Qty.	25 items

KWPN-M20/-185 90

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 185.4 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical data

Version DIN series 46235, 90°

Connectors

Conductor cross-section	185 mm ²	Insulation	not available
Hole	M 20	Inside diameter of shaft (d1)	19 mm
Outside diameter of shaft (d3)	25.5 mm	Shaft length (a)	40 mm
Connection length (l)	35.8 mm	Inside diameter of flange (d2)	21 mm
Flange width (b)	40 mm	Identification number Cu	25 K

Classifications

ETIM 8.0	EC001050	ETIM 9.0	EC001050
ETIM 10.0	EC001050	ECLASS 14.0	27-40-02-03
ECLASS 15.0	27-40-02-03		

KWPN-M20/-185 90

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

