



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|---|
| Version | cable lug, terminal end,300 mm ² |
| Order No. | 1498550000 |
| Type | KP-M14/-300 |
| GTIN (EAN) | 4050118307924 |
| Qty. | 10 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|---------|
| Net weight | 348.8 g |
|------------|---------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|---------|-------------------------------|
| Version | DIN series 46235, standard |
|---------|-------------------------------|

Connectors

| | | | |
|--------------------------------|---------------------|--------------------------------|---------------|
| Conductor cross-section | 300 mm ² | Insulation | not available |
| Hole | M 14 | Inside diameter of shaft (d1) | 24.5 mm |
| Outside diameter of shaft (d3) | 32 mm | Shaft length (a) | 50 mm |
| Connection length (l) | 104 mm | Inside diameter of flange (d2) | 15 mm |
| Flange width (b) | 48.5 mm | Identification number Cu | 32 K |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001050 | ETIM 9.0 | EC001050 |
| ETIM 10.0 | EC001050 | ECLASS 14.0 | 27-40-02-03 |
| ECLASS 15.0 | 27-40-02-03 | | |

Drawings

