

IE-CC-NM-SMAM-6M**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Version	Antenna cable, Connection 1:, N male, Connection 2:, SMA male, Length: 6 m
Order No.	1491210000
Type	IE-CC-NM-SMAM-6M
GTIN (EAN)	4050118300758
Qty.	1 items

IE-CC-NM-SMAM-6M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	6 m	Length (inches)	236.2205 inch
Net weight	223.4 g		

Temperatures

Storage temperature	-70 °C...85 °C	Operating temperature	-40 °C...85
---------------------	----------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Electrical properties of cable

Attenuation at 800 MHz	approx. 0.31 dB/m	Attenuation at 2000 MHz	approx. 0.5 dB/m
Characteristic impedance	50 Ω		

Mechanical and material properties of cable

UV-resistant	Yes	Sheath diameter	4.95 mm
Material sheath	Polyethylene	Min. bending radius, repetitive	50,8 mm
Min. bending radius, once only	12,7 mm		

Technical data

Type of connection	Connection 1:, N male, Connection 2:, SMA male
--------------------	---

Environmental conditions

Operating temperature, max.	85	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-70 °C

Classifications

ETIM 8.0	EC001682	ETIM 9.0	EC001682
ETIM 10.0	EC001682	ECLASS 14.0	27-06-03-10
ECLASS 15.0	27-06-03-10		

Drawings

Product image



Connection 1: SMA male

Product image



Connection 2: N-type male
