

**KRN-M6/-35 S****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|                 |                                                                                       |
|-----------------|---------------------------------------------------------------------------------------|
| Version         | cable lug, terminal end, 35 mm <sup>2</sup> , 35 mm <sup>2</sup> - 35 mm <sup>2</sup> |
| Order No.       | <a href="#">1494790000</a>                                                            |
| Type            | KRN-M6/-35 S                                                                          |
| GTIN (EAN)      | 4050118304466                                                                         |
| Qty.            | 25 items                                                                              |
| Delivery status | This article will no longer be available in the future.                               |
| Last order date | 2026-03-31T00:00:00+02:00                                                             |

## KRN-M6/-35 S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 19.28 g |
|------------|---------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Technical data

|         |                            |
|---------|----------------------------|
| Version | Euro series, narrow flange |
|---------|----------------------------|

## Connectors

|                                |                    |                                |                    |
|--------------------------------|--------------------|--------------------------------|--------------------|
| Conductor cross-section, max.  | 35 mm <sup>2</sup> | Conductor cross-section, min.  | 35 mm <sup>2</sup> |
| Conductor cross-section        | 35 mm <sup>2</sup> | Insulation                     | not available      |
| Hole                           | M 6                | Identification colour          | None               |
| Inside diameter of shaft (d1)  | 8.5 mm             | Outside diameter of shaft (d3) | 12 mm              |
| Shaft length (a)               | 17 mm              | Connection length (l)          | 33 mm              |
| Inside diameter of flange (d2) | 6.4 mm             | Flange width (b)               | 15 mm              |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001051    | ETIM 9.0    | EC001051    |
| ETIM 10.0   | EC001051    | ECLASS 14.0 | 27-40-02-05 |
| ECLASS 15.0 | 27-40-02-05 |             |             |

Drawings

