Data sheet

KRN-M12/-6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end,6 mm²,6 mm² - 6 mm²
Order No.	1497210000
Type	KRN-M12/-6
GTIN (EAN)	4050118306347
Qty.	100 items

KRN-M12/-6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	6.4 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Version	Euro series, standard

Connectors

Conductor cross-section, max.	6 mm²	Conductor cross-section, min.	6 mm²
Conductor cross-section	6 mm²	Insulation	not available
Hole	M 12	Identification colour	None
Inside diameter of shaft (d1)	3.5 mm	Outside diameter of shaft (d3)	6.5 mm
Shaft length (a)	9 mm	Connection length (l)	27.5 mm
Inside diameter of flange (d2)	13 mm	Flange width (b)	19 mm

Classifications

ETIM 8.0	EC001051	ETIM 9.0	EC001051
ETIM 10.0	EC001051	ECLASS 14.0	27-40-02-05
ECLASS 15.0	27-40-02-05		

KRN-M12/-6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings