

**KWPN-M16/-150 90****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|            |  |
|------------|--|
| Version    | cable lug, terminal end, 150 mm <sup>2</sup> |
| Order No.  | <a href="#">1497830000</a>                   |
| Type       | KWPN-M16/-150 90                             |
| GTIN (EAN) | 4050118307160                                |
| Qty.       | 25 items                                     |

## KWPN-M16/-150 90

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |          |
|------------|----------|
| Net weight | 148.26 g |
|------------|----------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Technical data

|         |                       |
|---------|-----------------------|
| Version | DIN series 46235, 90° |
|---------|-----------------------|

### Connectors

|                                |                     |                                |               |
|--------------------------------|---------------------|--------------------------------|---------------|
| Conductor cross-section        | 150 mm <sup>2</sup> | Insulation                     | not available |
| Hole                           | M 16                | Inside diameter of shaft (d1)  | 17 mm         |
| Outside diameter of shaft (d3) | 23.5 mm             | Shaft length (a)               | 35 mm         |
| Connection length (l)          | 30.8 mm             | Inside diameter of flange (d2) | 17 mm         |
| Flange width (b)               | 34 mm               | Identification number Cu       | 22 K          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001050    | ETIM 9.0    | EC001050    |
| ETIM 10.0   | EC001050    | ECLASS 14.0 | 27-40-02-03 |
| ECLASS 15.0 | 27-40-02-03 |             |             |

**KWPN-M16/-150 90**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

