

**CC-M 18/52 2X3 ST****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print. In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	MetalliCard, Device markers, 18 x 52 mm, silver
Order No.	<a href="#">1505350000</a>
Type	CC-M 18/52 2X3 ST
GTIN (EAN)	4050118313932
Qty.	200 items

## CC-M 18/52 2X3 ST

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.0197 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	52 mm	Width (inches)	2.0472 inch
Net weight	3.3 g		

### Temperatures

Operating temperature range	-55...130 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Version	pluggable, with 3.5 mm mounting hole	
Width	52 mm	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Colour	silver	
Basic material	Micro-etched stainless steel 1.4301 (ST)	
Printed characters	without	
Number of markers per packaging unit	Form of supply	MetalliCard
Size of labelling field	16 x 50 mm	
Recommended industries	Energy, Process	
compatible printer		
Number of markers per combination	1 MetalliCard = Device markers	
Operating temperature range	-55...130 °C	

### Device markers

Drill-hole diameter	3.30 mm
---------------------	---------

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Drawings**

