

## IE-SW-BL05T-1GT-4GTPOE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



- 4 x IEEE 802.3af/at compliant PoE ports
- 12/24/48 VDC redundant wide-range power supply
- Integrated DC/DC converter for supplying 48 V PoE devices over the entire input voltage range from 12 to 57 VDC
- Intelligent power consumption detection and classification
- Variations with copper and fibre-optic interface (multi-mode and singlemode)

### General ordering data

Version	Network switch, unmanaged PoE, Gigabit Ethernet, Number of ports: 4 * RJ45 10/100/1000BaseT(X) PoE+, 1 * RJ45 10/100/1000BaseT(X), IP30, -40 °C...75 °C
Order No.	<a href="#">1504340000</a>
Type	IE-SW-BL05T-1GT-4GTPOE
GTIN (EAN)	4050118312096
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2027-01-30T00:00:00+01:00
Alternative product	<a href="#">IE-SW-BLB-05-1GT-4GTPOE</a>

Creation date 06.04.2026 12:00:30 MEZ

Catalogue status / Drawings

## IE-SW-BL05T-1GT-4GTPOE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

## Dimensions and weights

Depth	105 mm	Depth (inches)	4.1338 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	29 mm	Width (inches)	1.1417 inch
Net weight	360 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5...95 %, no condensation		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

## EMC conformity and approvals

EMC standards	FCC Part 15 Subpart B Class A, EN 55032, EN 55024, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, EN 61000-4-8	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Safety standard	UL 508

## Environmental conditions

Operating temperature, max.	75 °C	Operating temperature, min.	-40 °C
Humidity	5...95 %, no condensation	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

## Interfaces

RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port	Function DIP switch	Activate/deactivate IEEE 802.3az energy-efficient Ethernet, Enable/disable jumbo frame support, Broadcast storm protection
------------	--	---------------------	--

## IE-SW-BL05T-1GT-4GTPOE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

Number of ports	4 * RJ45 10/100/1000BaseT(X) PoE+, 1 * RJ45 10/100/1000BaseT(X)	LED indicator	enable/disable, Switching between standard PoE (up to 30 W) and High Power PoE (up to 36 W) PWR1, PWR2, 10/100/1000M (TP-Port), PoE
-----------------	--	---------------	--

### MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	1257910 h

### Power over Ethernet (PoE)

PoE output power	Standard	IEEE 802.3af	
	Output power	15.4 W	
	Standard	IEEE 802.3at	
	Output power	30 W	
	Standard	High power mode (proprietary)	
PoE output current	Standard	IEEE 802.3af	
	Output current	350 mA	
	Standard	IEEE 802.3at	
	Output current	600 mA	
	Standard	High power mode (proprietary)	
Total PoE power budget	Output current	720 mA	
	Voltage type	DC	
	Voltage, min.	12 V	
	Voltage, max.	17 V	
	Power budget	62 W	
	Voltage type	DC	
	Voltage, min.	18 V	
	Voltage, max.	35 V	
	Power budget	120 W	
	Voltage type	DC	
	Voltage, min.	36 V	
	Voltage, max.	57 V	
	Power budget	144 W	
	PoE pin assignment	Mode A: Pin 1, 2 (V+); Pin 3, 6 (V-); Alternative A; MDI	

### Power supply

Reverse polarity protection	Yes	
Supply voltage	12/24/48 V DC, 2 redundant inputs	
Power consumption	max. 11.73 W (without PD's consumption)	
Inrush current	17.4 A at 24 V DC (0.1 to 1 ms)	
Power loss	36.4 BTU/h	
Overload current protection	Yes	
Connection type	2 removable 2-pole terminal blocks	
Voltage supply range	Voltage type	DC
	Voltage, min.	12 V
	Voltage, max.	57 V
Current consumption	Voltage	12 V
	Current	5.92 A
	Voltage	24 V
	Current	5.65 A
	Voltage	48 V

**IE-SW-BL05T-1GT-4GTPOE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

| Current 3.21 A

**Switch characteristics**

MAC table size	8 K	Packet buffer size	1024 kBit
Jumbo frame support	up to 10 KB		

**Technical data**

Housing main material	Aluminium	Type of mounting	DIN rail
Protection degree	IP30	Speed	Gigabit Ethernet
Switch	unmanaged PoE		

**Technology**

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3af for Power-over-Ethernet, IEEE 802.3at for Power-over-Ethernet, IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X), IEEE 802.3x for flow control, IEEE 802.3az Energy-Efficient Ethernet		

**Classifications**

ETIM 8.0	EC000734	ETIM 9.0	EC000734
ETIM 10.0	EC000734	ECLASS 14.0	19-17-04-02
ECLASS 15.0	19-17-04-02		

## IE-SW-BL05T-1GT-4GTPOE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



#### General ordering data

Type	RM-KIT	Version	
Order No.	<a href="#">1241440000</a>	Kit for 19"-rack mounting	
GTIN (EAN)	4050118029154		
Qty.	1 ST		

### Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components. IE-WALLMOUNT-KIT-30MM for use with:

- Industrial Ethernet Switches of the product range IE-SW-BL05

IE-WALLMOUNT-KIT-46MM for use with:

- Industrial Ethernet Switches of the product ranges IE-SW-BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18
- Industrial Ethernet media converters of the product range IE-MC-VL
- Industrial Ethernet switches of the product range IE-WL-AP

#### General ordering data

Type	IE-WALLMOUNT-KIT-30MM	Version	
Order No.	<a href="#">1504450000</a>	Kit for wall mounting	
GTIN (EAN)	4050118312300		
Qty.	1 ST		

### Ethernet



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

## IE-SW-BL05T-1GT-4GTPOE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### General ordering data

Type	VDATA CAT6	Version	
Order No.	<a href="#">1348590000</a>	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,	
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4	
Qty.	1 ST		