Data sheet

# PAC-MIMQ-4X10-V0-4M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the TERMSERIES relay modules. These cables consist of the following components:
• Manufacturer's PLC connector.
• Multi-pole LIYY cable with a cross-section of 0.14mm².
• 10-pole flat cable connectors.
The cables are tested automatically for continuity and insulation to ensure the functionality for which they have been designed.

## General ordering data

| | |
|---|---|
| Version | Pre-assembled cable, PAC, Cable LiYY, 5.4 ± 1 mm |
| Order No. | 1512290040 |
| Type | PAC-MIMQ-4X10-V0-4M |
| GTIN (EAN) | 4099986589766 |
| Qty. | 1 items |

# PAC-MIMQ-4X10-V0-4M

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 667 g |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

### General Data

| | | | |
|---|---|---|---|
| Cable length | 4 m | Suitable for | Digital signals |
| Basic material | PVC | Cable | Cable LiYY |
| Interface connector | 4xHE10 10P | Number of poles, min. | 10-pole |
| Outer diameter | 5.4 ± 1 mm | Connector PLC side | FUJITSU FCN363J040 40P |
| Wire cross-section | 0.14 mm² | | |

### Electrical Data

| | | | |
|---|---|---|---|
| Total current, max. | 3 A | High voltage test | 1 KV/1s |
| Permissible current strength per path, max. | 1 A | Rated voltage | ≤ 60 V DC ≤ 25 V AC |
| Resistance | ≤ 150 mΩ/m | Capacity (wire / wires) | 300 pF/m |

### Rated data UL

| | |
|---|---|
| Total current, max. | 3 A |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |