

PAC-MIMQ-4X10-V3-5M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the TER-MSERIES relay modules. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY cable with a cross-section of 0.14mm².
- 10-pole flat cable connectors.

The cables are tested automatically for continuity and insulation to ensure the functionality for which they have been designed.

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYY, 5.4 ± 1 mm
Order No.	1512330050
Type	PAC-MIMQ-4X10-V3-5M
GTIN (EAN)	4099986591462
Qty.	1 items

PAC-MIMQ-4X10-V3-5M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Net weight	832 g
------------	-------

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General Data

Cable length	5 m	Suitable for	Digital signals
Basic material	PVC	Cable	Cable LiYY
Interface connector	4xHE10 10P	Number of poles, min.	10-pole
Outer diameter	5.4 ± 1 mm	Connector PLC side	FUJITSU FCN363J040 40P
Wire cross-section	0.14 mm ²		

Electrical Data

Total current, max.	3 A	High voltage test	1 kV/1s
Permissible current strength per path, max.	1 A	Rated voltage	≤ 60 V DC ≤ 25 V AC
Resistance	≤ 150 mΩ/m	Capacity (wire / wires)	300 pF/m

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		