

SAIE-M12B-4-1.0U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, Female socket, straight, Mounting thread: M 16 x 1.5, Number of poles: 4, Strand / cable length: 1 m, Front mounting
Order No.	1513040000
Type	SAIE-M12B-4-1.0U-M16
GTIN (EAN)	4050118320558
Qty.	1 items

SAIE-M12B-4-1.0U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

Net weight 35 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

PE function	No	Core cross-section	0.34 mm ²
Strand / cable length	1 m	Colour coding	brown, white, blue, black
Number of poles	4		

Technical data customisable plug-in connectors

Number of poles	4	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Zinc diecast
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Temperature range of housing	-30...+90 °C		

Standards

Connector standard IEC 61076-2-101

General data

Number of poles	4
Coding	A-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.34 mm ²
Housing main material	Zinc diecast
Type of mounting	Front mounting
Nominal voltage	250 V
Nominal current	4 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Connection 1	M12
Connection 2	Flying wires
Strand / cable length	1 m
Mounting thread	M 16 x 1.5
Mounting torque range	2 Nm

SAIE-M12B-4-1.0U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Technical data

Mounting torque	max.	2 Nm
Temperature range of housing	-30...+90 °C	
Conductor O.D.	-	

Classifications

ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

Wiring diagram



Pole scheme

