

**PAC-YOKO-4X10-V1-1M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the TER-MSERIES relay modules. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY cable with a cross-section of 0.14mm<sup>2</sup>.
- 10-pole flat cable connectors.

The cables are tested automatically for continuity and insulation to ensure the functionality for which they have been designed.

**General ordering data**

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 5.4 ± 1 mm |
| Order No.  | <a href="#">1512210015</a>                       |
| Type       | PAC-YOKO-4X10-V1-1M5                             |
| GTIN (EAN) | 4099986591127                                    |
| Qty.       | 1 items  |

**PAC-YOKO-4X10-V1-1M5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 257 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 4bbf2c0d-0764-4fc8-bb24-9351c28c190d

**General Data**

|                     |                      |                       |                 |
|---------------------|----------------------|-----------------------|-----------------|
| Cable length        | 1.5 m                | Suitable for          | Digital signals |
| Basic material      | PVC                  | Cable                 | Cable LiYY      |
| Interface connector | 4xHE10 10P           | Number of poles, min. | 10-pole         |
| Outer diameter      | 5.4 ± 1 mm           | Connector PLC side    | HE10 50 P       |
| Wire cross-section  | 0.14 mm <sup>2</sup> |                       |                 |

**Electrical Data**

|   |            |                       |                     |
|---|------------|-----------------------|---------------------|
| Total current, max.                         | 3 A        | High voltage test     | 1 KV/1s             |
| Permissible current strength per path, max. | 1 A        | Rated voltage         | ≤ 60 V DC ≤ 25 V AC |
| Resistance                                  | ≤ 150 mΩ/m | Capacity wire / wires | 300 pF/m            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |