




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

| Version | Feed-through terminal, PUSH IN, $2.5\ mm^2$, $800\ V$, $24\ A$, orange |
|------------|---|
| Order No. | <u>1521930000</u> |
| Туре | A2C 2.5 OR |
| GTIN (EAN) | 4050118328264 |
| Qty. | 100 items |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Aр | pro | ova | ıls |
|----|-----|-----|-----|
|----|-----|-----|-----|

Approvals



| | House | |
|---------------------------|-------------------|--|
| ROHS | Conform | |
| UL File Number Search | <u>UL Website</u> | |
| Certificate No. (cURus) | E60693 | |
| Certificate No. (cURusEX) | E184763 | |

Dimensions and weights

| Depth | 36.5 mm | Depth (inches) | 1.437 inch |
|--------------------------|-------------|----------------|------------|
| Depth including DIN rail | 37 mm | Height | 55 mm |
| Height (inches) | 2.1654 inch | Width | 5.1 mm |
| Width (inches) | 0.2008 inch | Net weight | 6.36 g |

Temperatures

| Storage temperature | -25 °C55 °C | Ambient temperature | -5 °C40 °C |
|----------------------------------|-------------|----------------------------------|------------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| RoHS Compliance Status | Compliant without exemption |
|------------------------|-----------------------------|
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| Basic material | Wemid | Colour | orange | |
|--------------------------------|--------|---------------------------|--------|--|
| Colour of operational elements | orange | UL 94 flammability rating | V-0 | |

Rating data IECEx/ATEX

| Certificate No. (ATEX) | TUEV16ATEX7909U | Certificate No. (IECEX) | IECEXTUR16.0036U |
|--------------------------------|---------------------|---------------------------------|---------------------|
| Max. voltage (ATEX) | 550 V | Current (ATEX) | 20 A |
| Wire cross section max. (ATEX) | 2.5 mm ² | Max. voltage (IECEX) | 550 V |
| Current (IECEX) | 20 A | Wire cross section max. (IECEX) | 2.5 mm ² |
| Marking EN 60079-7 | Ex eb II C Gb | Ex 2014/34/EU label | II 2 G D |

System specifications

| End cover plate required | Yes | Number of potentials | 1 |
|-------------------------------|-----|-------------------------------------|-------|
| Number of levels | 1 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | No | Mounting rail | TS 35 |
| N-function | No | PE function | No |
| PEN function | No | | |





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Additional technical data

| With snap-in pegs | No | Open sides | right | |
|---------------------|-------|--------------------------|---------|--|
| Snap-on | No | Type of fixing | Snap-on | |
| Installation advice | Rail | Explosion-tested version | Yes | |
| Type of mounting | TS 35 | | | |

CSA rating data

| Wire cross section max. (CSA) | 12 AWG | Voltage size C (CSA) | 600 V |
|-------------------------------|--------|-----------------------|-----------------|
| Current size C (CSA) | 20 A | Certificate No. (CSA) | 200039-70089609 |
| Voltage size B (CSA) | 600 V | Current size B (CSA) | 20 A |
| Voltage size D (CSA) | 600 V | Current size D (CSA) | 5 A |
| Wire cross section min. (CSA) | 28 AWG | | |

Conductors for clamping (additional connection)

Connection type, additional connection PUSH IN

Conductors for clamping (rated connection)

| Gauge to IEC 60947-1 | A3 |
|---|----------------------|
| Wire connection cross section AWG, max. | AWG 12 |
| Connection direction | top |
| Stripping length | 10 mm |
| Type of connection | PUSH IN |
| Number of connections | 2 |
| Clamping range, max. | 4 mm ² |
| Clamping range, min. | 0.14 mm ² |
| Blade size | 0.6 x 3.5 mm |
| Wire connection cross section AWG, min. | AWG 28 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm ² |
| Wire connection cross section, finely stranded, max. | 4 mm ² |
| Wire connection cross section, finely stranded, min. | 0.14 mm ² |
| Connection cross-section, stranded, max. | 4 mm ² |
| Connection cross-section, stranded, mi | n. 0.14 mm² |
| Twin wire-end ferrules, max. | 0.75 mm ² |
| Twin wire-end ferrules, min. | 0.5 mm ² |
| Wire connection cross-section, solid | 2.5 mm ² |
| core, max. | |
| Wire connection cross-section, solid core, min. | 0.14 mm ² |
| Connection cross-section, finely stranded, min. | 0.14 mm ² |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Tube length for wire-end ferrule with | Tube length | min. | 6 mm |
|--|--|---------------|----------------------|
| plastic collar DIN 46228/4 | | max. | 8 mm |
| | Cross-section for conductor connection | min. | 0.14 mm ² |
| | | max. | 0.34 mm ² |
| | Tube length | min. | 6 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm² |
| | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 1.5 mm ² |
| | | max. | 2.5 mm ² |
| Tube length for twin wire-end ferrule | Tube length | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 0.75 mm ² |
| Tube length for wire-end ferrule without | Tube length | nominal | 5 mm |
| plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal | 0.25 mm ² |
| | Tube length | min. | 6 mm |
| | | max. | 10 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 7 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 1.5 mm ² |
| | | max. | 4 mm ² |
| Tube length for wire-end ferrule with | Tube length, min. | 6 mm | |
| plastic collar acc. to cross-section | Tube length, max. | 8 mm | |
| | Tube length, min. 6 mm | | |
| | Tube length, max. 12 mm | | |
| | Tube length, min. | 8 mm | |
| | Tube length, max. | 12 mm | |
| Tube length for wire-end ferrule without | Tube length, min. | 5 mm | |
| plastic collar acc. to cross-section | Tube length, max. | 5 mm | |
| | Tube length, min. | 6 mm | |
| | Tube length, max. | 10 mm | |
| | Tube length, min. | 7 mm | |
| | | 12 mm | |
| | Tube length, max. | 12 mm | |
| Tube length for twin wire-end ferrule | Tube length, max. Tube length, min. | 12 mm 8 mm | |

General

| Wire connection cross section AWG, | AWG 12 | Installation advice | Rail |
|------------------------------------|--------|---------------------|---------------|
| max. | | | |
| Wire connection cross section AWG, | AWG 28 | Standards | IEC 60947-7-1 |
| min. | | | |
| Mounting rail | TS 35 | | |

Rating data

| Rated cross-section | 2.5 mm ² | Rated voltage | 800 V |
|--|---------------------|---------------------------------|---------------|
| Rated DC voltage | 800 V | Nominal current | 24 A |
| Current at maximum wires | 24 A | Standards | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ | Rated impulse withstand voltage | 8 kV |

Creation date 03.11.2025 03:48:59 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

| Power loss in accordance with IEC 60947-7-x | 0.77 W | Surge voltage category | III |
|---|--------|------------------------|-----|
| Pollution severity | 3 | | |

UL rating data

| Conductor size Factory wiring max. (cURus) | 12 AWG | Voltage size B (cURus) | 600 V |
|--|------------|--|--------|
| Voltage size D (cURus) | 600 V | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cUR | us) 28 AWG | Conductor size Factory wiring min. (cURus) | 28 AWG |
| Current size B (cURus) | 20 A | Voltage size C (cURus) | 600 V |
| Current size C (cURus) | 20 A | Current size D (cURus) | 5 A |
| Conductor size Field wiring max. (cUF | Rus)12 AWG | | |

Classifications

| EC000897 | ETIM 7.0 | EC000897 |
|-------------|---|---|
| EC000897 | ETIM 9.0 | EC000897 |
| EC000897 | ECLASS 9.0 | 27-14-11-20 |
| 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |
| 27-25-01-01 | ECLASS 14.0 | 27-25-01-01 |
| 27-25-01-01 | | |
| | EC000897 EC000897 27-14-11-20 27-14-11-20 27-25-01-01 | EC000897 ETIM 9.0 EC000897 ECLASS 9.0 27-14-11-20 ECLASS 10.0 27-14-11-20 ECLASS 12.0 27-25-01-01 ECLASS 14.0 |

Data sheet

A2C 2.5 OR




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

End plates and partition plates



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| Туре | AEP 2C 2.5 | Version |
|------------|-------------------|---------------------|
| Order No. | <u>1514400000</u> | A-series, End plate |
| GTIN (EAN) | 4050118436112 | |
| Qty. | 50 ST | |
| Туре | AEP 2C 2.5 BL | Version |
| Order No. | <u>1514420000</u> | A-series, End plate |
| GTIN (EAN) | 4050118436136 | |
| Qty. | 50 ST | |
| Туре | AEP 2C 2.5 OR | Version |
| Order No. | 2052290000 | A-series, End plate |
| GTIN (EAN) | 4050118411959 | |
| Qty. | 50 ST | |

End bracket









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| Туре | AEB 35 SC/1 | Version |
|------------|---------------|-----------------------|
| Order No. | 1991920000 | A-series, End bracket |
| GTIN (EAN) | 4050118376722 | |
| Qty. | 50 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Testadapter and testsockets









Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| Туре | ATPG 2.5 MI-R | Version |
|---|---|---|
| Order No. | <u>1991960000</u> | Test adapter (terminal), 1.5 mm ² , 250 V, 0.2 A |
| GTIN (EAN) | 4050118376685 | |
| Qty. | 50 ST | |
| Туре | ATPG 2.5/3 | Version |
| Order No. | 2041190000 | Test adapter (terminal), 1.5 mm², 250 V, 0.2 A |
| GTIN (EAN) | 4050118409604 | |
| Qty. | 25 ST | |
| • | | |
| Туре | ATPG 2.5/5 | Version |
| | | Version Test adapter (terminal), 1.5 mm², 250 V, 0.2 A |
| Туре | ATPG 2.5/5 | |
| Type Order No. | ATPG 2.5/5 2041180000 | |
| Type Order No. GTIN (EAN) | ATPG 2.5/5 2041180000 4050118409505 | |
| Type Order No. GTIN (EAN) Oty. | ATPG 2.5/5 2041180000 4050118409505 25 ST | Test adapter (terminal), 1.5 mm², 250 V, 0.2 A |
| Type Order No. GTIN (EAN) Oty. | ATPG 2.5/5 2041180000 4050118409505 25 ST ATPG 1.5-10 L | Test adapter (terminal), 1.5 mm², 250 V, 0.2 A Version |

Cross-connections









The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| Туре | ZQV 2.5N/10 | Version |
|-------------------|------------------------------|---|
| Order No. | <u>1527690000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118447989 | 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm |
| Qty. | 20 ST | |
| | | |
| Туре | ZQV 2.5N/10 BL | Version |
| Type Order No. | ZQV 2.5N/10 BL 1527880000 | Version Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10, |
| | , | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

| Type | 70V 2 5N /10 PD | Version |
|-------------------|------------------------------------|--|
| Type Order No. | ZQV 2.5N/10 RD | Version Cross-connector (terminal) Plugged red 24 A Number of poles: 10 |
| GTIN (EAN) | <u>2108910000</u> 4050118486018 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm |
| | | Fitch in min (F). 5.10, insulated. 1es, Width. 40.7 min |
| Qty. | 20 ST | Version |
| Type Order No. | ZQV 2.5N/2 | |
| | <u>1527540000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448467 60 ST | 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm |
| Qty. | | y : |
| Туре | ZQV 2.5N/2 BL | Version |
| Order No. | <u>1527740000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2, |
| GTIN (EAN) | 4050118448658 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm |
| Qty. | 60 ST | v · |
| Туре | ZQV 2.5N/2 RD | Version |
| Order No. | <u>2108470000</u> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2, |
| GTIN (EAN) | 4050118448542 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/20 | Version |
| Order No. | 1527720000 | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118447972 | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm |
| Qty. | 20 ST | |
| Type | ZQV 2.5N/20 BL | Version |
| Order No. | <u>1527890000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118448566 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/20 RD | Version |
| Order No. | <u>2108920000</u> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118485899 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/3 | Version |
| Order No. | <u>1527570000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448450 | 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/3 BL | Version |
| Order No. | <u>1527770000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3, |
| GTIN (EAN) | 4050118448641 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/3 RD | Version |
| Order No. | 2108690000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3, |
| GTIN (EAN) | 4050118448535 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/4 | Version |
| Order No. | <u>1527590000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448443 | 4, Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/4 BL | Version |
| Order No. | <u>1527780000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4, |
| GTIN (EAN) | 4050118448634 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm |
| Qty. | 60 ST | |
| Туре | ZQV 2.5N/4 RD | Version |
| Order No. | 2108700000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4, |
| GTIN (EAN) | 4050118448528 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm |
| Qty. | 60 ST | |
| | - | |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

| Туре | ZQV 2.5N/5 | Version |
|------------|------------------------------------|---|
| Order No. | | |
| GTIN (EAN) | <u>1527620000</u> 4050118448436 | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: 5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm |
| , , | | 5, Filch in min (F). 5. 10, insulated. Tes, Widur. 23.2 min |
| Qty. | 20 ST | w · |
| Туре | ZQV 2.5N/5 BL | Version |
| Order No. | <u>1527790000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5, |
| GTIN (EAN) | 4050118448627 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/5 RD | Version |
| Order No. | <u>2108710000</u> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5, |
| GTIN (EAN) | 4050118448511 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/50 | Version |
| Order No. | <u>1527730000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118411362 | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm |
| Qty. | 5 ST | |
| Туре | ZQV 2.5N/50 BL | Version |
| Order No. | 1527920000 | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118448559 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm |
| Qty. | 5 ST | |
| Туре | ZQV 2.5N/50 RD | Version |
| Order No. | 2109000000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118486001 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm |
| Qty. | 5 ST | |
| Туре | ZQV 2.5N/6 | Version |
| Order No. | 1527630000 | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448429 | 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/6 BL | Version |
| Order No. | 1527820000 | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6, |
| GTIN (EAN) | 4050118448610 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/6 RD | Version |
| Order No. | 2108720000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6, |
| GTIN (EAN) | 4050118448504 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/7 | Version |
| Order No. | <u>1527640000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448412 | 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/7 BL | Version |
| Order No. | 1527830000 | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7, |
| GTIN (EAN) | 4050118448603 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm |
| Qty. | 20 ST | (),, |
| Туре | ZQV 2.5N/7 RD | Version |
| Order No. | 2108810000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7, |
| GTIN (EAN) | 4050118448498 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm |
| Qty. | 20 ST | т кол ит пин (т.). 3. 10, почиваеч. 165, уунция. 33.4 пин |
| | | Varian |
| Type | ZQV 2.5N/8 | Version Cross connector (terminal). Plugged energy 24.4. Number of noise: |
| Order No. | <u>1527670000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118448405 | 8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm |
| Qty. | 20 ST | |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

| Туре | ZQV 2.5N/8 BL | Version |
|------------|-------------------|--|
| Order No. | <u>1527840000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4050118448597 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/8 RD | Version |
| Order No. | 2108870000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4050118448481 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/9 | Version |
| Order No. | <u>1527680000</u> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles: |
| GTIN (EAN) | 4050118447996 | 9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/9 BL | Version |
| Order No. | <u>1527870000</u> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4050118448580 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm |
| Qty. | 20 ST | |
| Туре | ZQV 2.5N/9 RD | Version |
| Order No. | 2108900000 | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4050118448474 | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm |
| Qty. | 20 ST | |

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | DEK 5/5 MC NE BR | Version |
|------------|-------------------|---|
| Order No. | <u>1249870000</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118051865 | Weidmueller, brown |
| Qty. | 1000 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

V0



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | DEK 5/5 MC NE VO WS |
|------------|---------------------|
| Order No. | <u>1388530000</u> |
| GTIN (EAN) | 4050118188622 |

1000 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, white

Blank

Qty.



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | DEK 5/5 MC NE VI | Version |
|------------|------------------|---|
| Order No. | 1249860000 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118042764 | Weidmueller, violet |
| Qty. | 1000 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | DEK 5/5 MC SDR |
|------------|----------------|
| Order No. | 1609810000 |
| GTIN (EAN) | 4008190456597 |
| Qty. | 200 ST |

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, To customer specification

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | DEK 5/5 MC NE BL | Version |
|-------------------|--------------------------------|--|
| Order No. | 1609801693 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397166 | Weidmueller, blue |
| Qty. | 1000 ST | |
| | | |
| Type | DEK 5/5 MC NE GE | Version |
| Type Order No. | DEK 5/5 MC NE GE 1609801687 | Version Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| • • | · · | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

| Type | DEK 5/5 MC NE GN | Version |
|---|--|---|
| Order No. | <u>1609801688</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397142 | Weidmueller, green |
| Qty. | 1000 ST | |
| Туре | DEK 5/5 MC NE GR | Version |
| Order No. | <u>1609801691</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397159 | Weidmueller, grey |
| Qty. | 1000 ST | |
| Туре | DEK 5/5 MC NE OR | Version |
| Order No. | <u>1238340000</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118062632 | Weidmueller, orange |
| Qty. | 1000 ST | |
| Туре | DEK 5/5 MC NE RT | Version |
| Order No. | <u>1609801686</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4008190397128 | Weidmueller, red |
| | | |
| Qty. | 1000 ST | |
| Qty. Type | 1000 ST DEK 5/5 MC NE SW | Version |
| - | | Version Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| Туре | DEK 5/5 MC NE SW | |
| Type Order No. | DEK 5/5 MC NE SW 1457550000 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| Type Order No. GTIN (EAN) | DEK 5/5 MC NE SW 1457550000 4050118263817 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| Type Order No. GTIN (EAN) Qty. | DEK 5/5 MC NE SW 1457550000 4050118263817 1000 ST | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, black |
| Type Order No. GTIN (EAN) Oty. Type | DEK 5/5 MC NE SW 1457550000 4050118263817 1000 ST DEK 5/5 MC NE WS | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, black Version |
| Type Order No. GTIN (EAN) Oty. Type Order No. | DEK 5/5 MC NE SW 1457550000 4050118263817 1000 ST DEK 5/5 MC NE WS 1609801044 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, black Version Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |

Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | DEK 5/5 PLUS MC NE GE | Version |
|-------------------|-------------------------------------|---|
| Order No. | <u>1907520000</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4032248532100 | Weidmueller, yellow |
| Qty. | 1000 ST | |
| | | |
| Type | DEK 5/5 PLUS MC NE WS | Version |
| Type Order No. | DEK 5/5 PLUS MC NE WS 1854490000 | Version Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| | | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- · Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | DEK 5/5 PLUS MC SDR |
|------------|---------------------|
| Order No. | <u>1854500000</u> |
| GTIN (EAN) | 4032248393602 |

200 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, To customer specification

Blank

Qty.



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | DEK 5/5 S MC NE WS | Version |
|------------|--------------------|---|
| Order No. | 1341620000 | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118145793 | Weidmueller, white |
| Qty. | 400 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | DEK 5/5 S MC SDR | Version |
|-------------------|-------------------------------------|--|
| Order No. | <u>1341590000</u> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 |
| GTIN (EAN) | 4050118146042 | Weidmueller, To customer specification |
| Qty. | 80 ST | |
| | | |
| Туре | WS 10/5 M PLUS MC SDR | Version |
| Type Order No. | WS 10/5 M PLUS MC SDR 2007770000 | Version WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| | · · | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 10/5 M PLUS MC NE WS | Version |
|-------------------|----------------------------------|--|
| Order No. | 2003770000 | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4050118424447 | Allen-Bradley, white |
| Qty. | 600 ST | |
| | | |
| Туре | WS 10/5 M MC NE WS | Version |
| Type Order No. | WS 10/5 M MC NE WS 1792000000 | Version WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| | , | |

Creation date 03.11.2025 03:48:59 MEZ




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 10/5 MC M SDR |
|------------|-------------------|
| Order No. | <u>1792010000</u> |
| GTIN (EAN) | 4032248223879 |
| Qty. | 144 ST |

Version

WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,

Allen-Bradley, To customer specification

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised

character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 10/5 MC NE BL | Version |
|------------|-------------------|--|
| Order No. | <u>1773531693</u> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141814 | Allen-Bradley, blue |
| Qty. | 720 ST | |
| Туре | WS 10/5 MC NE GE | Version |
| Order No. | <u>1773531687</u> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141753 | Allen-Bradley, yellow |
| Qty. | 720 ST | |
| Туре | WS 10/5 MC NE RT | Version |
| Order No. | <u>1773531686</u> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141746 | Allen-Bradley, red |
| Qty. | 720 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

 Type
 WS 10/5 MC NE WS
 Version

 Order No.
 1635000000
 WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,

 GTIN (EAN)
 4008190261948
 Allen-Bradley, white

 Qty.
 720 ST

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 10/5 MC SDR | Version |
|------------|-------------------|--|
| Order No. | <u>1635010000</u> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190456634 | Allen-Bradley, To customer specification |
| Qty. | 144 ST | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 10/5 PLUS MC NE WS | Version |
|------------|-----------------------|--|
| Order No. | 1046380000 | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248782086 | Allen-Bradley, white |
| Qty. | 600 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type WS 10/5 PLUS MC SDR
Order No. 1046320000
GTIN (EAN) 4032248782024
Qty. 120 ST

Version

WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,

Allen-Bradley, To customer specification

DEK 5/5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- · Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

| Туре | DEK 5/5 MM WS | Version |
|------------|---------------|--|
| Order No. | 2007110000 | Dekafix, Terminal marker, 5 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118391862 | |
| Qty. | 800 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

WS 8/5



WS/DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

| Туре | WS 8/5 MM WS | Version |
|------------|---------------|---|
| Order No. | 2007150000 | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392029 | |
| Qty. | 800 ST | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 8/5 MC NE BL | Version |
|-------------------|---|---|
| Order No. | <u>1773521693</u> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141715 | Allen-Bradley, blue |
| Qty. | 720 ST | |
| | | |
| Туре | WS 8/5 MC NE GE | Version |
| Type Order No. | WS 8/5 MC NE GE 1773521687 | Version WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| | , | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

| Туре | WS 8/5 MC NE OR | Version |
|------------|-------------------|---|
| Order No. | <u>1773521690</u> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248143092 | Allen-Bradley, orange |
| Qty. | 720 ST | |
| Туре | WS 8/5 MC NE RT | Version |
| Order No. | <u>1773521686</u> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248141531 | Allen-Bradley, red |
| Qty. | 720 ST | |
| Туре | WS 8/5 MC NE WS | Version |
| Order No. | 1640740000 | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190279103 | Allen-Bradley, white |
| Qty. | 720 ST | |

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 8/5 MC SDR | Version |
|------------|-------------------|---|
| Order No. | <u>1640750000</u> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190456627 | Allen-Bradley, To customer specification |
| Qty. | 144 ST | |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is

- · Can be fitted in strips or individually
- Markers in proven MultiCard format For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

| Туре | WS 8/5 PLUS MC NE WS | Version |
|------------|----------------------|---|
| Order No. | <u>1951870000</u> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248631605 | Allen-Bradley, white |
| Qty. | 600 ST | |

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- · Can be fitted in strips or individually
- Markers in proven MultiCard format For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Туре | WS 8/5 PLUS MC SDR | Version |
|------------|--------------------|---|
| Order No. | 1038790000 | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248768066 | Allen-Bradley, To customer specification |
| Qty. | 120 ST | |

Digital current clamp devices



Digital current clamp devices and attachments and adapters are used for measuring AC and DC currents. The significant advantage of these devices is that you can make a measurement without breaking the flow of current.

General ordering data

| Туре | ZUB MULTIMETER | Version |
|-----------|------------------|------------|
| Order No. | 9205270000 | Multimeter |
| GTIN (EAN | N) 4032248723522 | |
| Qty. | 1 ST | |

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

End bracket









that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

Weidmüller's range of products includes end brackets

General ordering data

Type AEB 35 SC/1 BK
Order No. 2475310000
GTIN (EAN) 4050118487114

Version A-series, End bracket

Qty. 50 ST

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

| Type | BZT 1 WS 10/5 | Version |
|-------------------|--------------------------------|------------------------------------|
| Order No. | <u>1805490000</u> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231 | |
| Qty. | 100 ST | |
| | | |
| Туре | BZT 1 ZA WS 10/5 | Version |
| Type Order No. | BZT 1 ZA WS 10/5 1805520000 | Version Accessories, Marker holder |
| | , | |

End plates and partition plates



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

Creation date 03.11.2025 03:48:59 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

| Туре | APP 1 |
|------------|---------------|
| Order No. | 2488970000 |
| GTIN (EAN) | 4050118499216 |
| Qtv. | 50 ST |

Version
A-series, Partition plate

Warning cover



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

General ordering data

| Type | AAM 2.5 YE FLASH |
|------------|------------------|
| Order No. | 2635550000 |
| GTIN (EAN) | 4050118674095 |
| Qty. | 40 ST |

Version

A-series, Terminal marker, 8 x 5.1 mm, Pitch in mm (P): 5.00 yellow

End bracket









Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| Туре | AEB 35 SCL/1 V0 | Version |
|---------------------------------|---|--------------------------------|
| Order No. | <u>2661280000</u> | A-series, End bracket |
| GTIN (EAN) | 4050118702163 | |
| Qty. | 20 ST | |
| Туре | AEB 35 SCL/1 VO BK | Version |
| Order No. | <u>2661300000</u> | A-series, End bracket |
| GTIN (EAN) | 4050118702187 | |
| Qty. | 20 ST | |
| | | |
| Туре | AEB 35 SCL/1 V0 GY | Version |
| Type Order No. | AEB 35 SCL/1 V0 GY 2661290000 | Version A-series, End bracket |
| | ' | |
| Order No. | <u>2661290000</u> | |
| Order No. GTIN (EAN) | 2661290000 4050118702170 | |
| Order No. GTIN (EAN) Qty. | 2661290000 4050118702170 20 ST | A-series, End bracket |
| Order No. GTIN (EAN) Oty. Type | 2661290000 4050118702170 20 ST ZST 1 | A-series, End bracket Version |

Creation date 03.11.2025 03:48:59 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Туре Order No.

ZST 1678680000

GTIN (EAN) 4008190466770

10 ST Qty.

Version Z-series, Accessories holder

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadiummolybdenum steel, gun-metal finish.

General ordering data

Туре Order No. GTIN (EAN)

Qty.

SDIS SLIM 0.6X3.5X100 2749610000

4050118896350

Version

Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade

thickness (A): 0.6 mm