

IE-C5DS4VG0750A60A60-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 75 m
Order No.	1522100750
Type	IE-C5DS4VG0750A60A60-E
GTIN (EAN)	4050118464405
Qty.	1 items

IE-C5DS4VG0750A60A60-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	75 m	Length (inches)	2952.7559 inch
Net weight	1300 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Installation temperature	-40 °C...80 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Cable specific standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, wire material	DIN EN 13602 Cu-ETP-A
Standard, assembly	UL-Style 21694	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, additional standards	UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8		

Standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, wire material	DIN EN 13602 Cu-ETP-A
Standard, assembly	UL-Style 21694	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, additional standards	UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8		

Cable structure

Strands	7	Sheathing colour	green (RAL 6018)
Standard designations	2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN	Cross-section	4*AWG 22/7 - 0.32 mm ²
Shielding	SF/UTP	Number of wires	4
Insulation cross-section	1.5 mm	Insulation	PE
Sheath diameter, max.	6.7 mm	Sheath diameter, min.	6.3 mm
Material sheath	PVC	Filler	As central element

IE-C5DS4VG0750A60A60-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Arrangement of wire cores	Star-quad	Complete shielding	Aluminium foil, Shielding braid made from copper wiring
Overlap of shielding braid	85 %	Wire material	Stranded tin-plated copper wire
Diameter of inner sheathing	4.05 mm	Sheathing material thickness	0.9 mm
Colour sequence or wires - wire pairs	white, yellow, blue, orange	Shielding braid thickness	0.13 mm

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Loop resistance	120 Ω/km
Signal propagation time	5.3 ns/m	Test voltage: wire-wire-shield	2000 Veff, 50 Hz, 1 min
Operating voltage, UL	600 V	Operating voltage (UL rating)	600 V
Transfer impedance	20 mΩ/m at 10 MHz	Characteristic impedance	100 ± 5 Ω at 100MHz

Mechanical and material properties of cable

Halogen	Yes	Min. bending radius, repetitive	7.5 x cable diameter
Min. bending radius, once only	3.5 *diameter	Abrasion resistance	good
Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685		

Plug, left

Plug left	RJ45, IP20, male contact, straight, plug, Plastic, shielded
-----------	---

Plug, right

Plug right	RJ45, IP20, male contact, straight, plug, Plastic, shielded
------------	---

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Drawings

Wiring

RJ45		RJ45
1	yellow	1
2	orange	2
3	white	3
6	blue	6