

IE-C5DS4VG0150A60A60-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Version | System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 15 m |
| Order No. | 1522100150 |
| Type | IE-C5DS4VG0150A60A60-E |
| GTIN (EAN) | 4050118333725 |
| Qty. | 1 items |

IE-C5DS4VG0150A60A60-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|-------|-----------------|---------------|
| Length | 15 m | Length (inches) | 590.5512 inch |
| Net weight | 940 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Cable specific standards

| | | | |
|-------------------------------|---|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, wire material | DIN EN 13602 Cu-ETP-A |
| Standard, assembly | UL-Style 21694 | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |

Standards

| | | | |
|-------------------------------|---|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, wire material | DIN EN 13602 Cu-ETP-A |
| Standard, assembly | UL-Style 21694 | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |

Cable structure

| | | | |
|---------------------------------------|--|------------------------------|---|
| Strands | 7 | Sheathing colour | green (RAL 6018) |
| Standard designations | 2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN | Cross-section | 4*AWG 22/7 - 0.32 mm ² |
| Shielding | SF/UTP | Number of wires | 4 |
| Insulation cross-section | 1.5 mm | Insulation | PE |
| Sheath diameter, max. | 6.7 mm | Sheath diameter, min. | 6.3 mm |
| Material sheath | PVC | Filler | As central element |
| Arrangement of wire cores | Star-quad | Complete shielding | Aluminium foil. Shielding braid made from copper wiring |
| Overlap of shielding braid | 85 % | Wire material | Stranded tin-plated copper wire |
| Diameter of inner sheathing | 4.05 mm | Sheathing material thickness | 0.9 mm |
| Colour sequence or wires - wire pairs | white, yellow, blue, orange | Shielding braid thickness | 0.13 mm |

IE-C5DS4VG0150A60A60-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical properties of cable

| | | | |
|-------------------------|--|--------------------------------|-------------------------|
| Category | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Loop resistance | 120 Ω/km |
| Signal propagation time | 5.3 ns/m | Test voltage: wire-wire-shield | 2000 Veff, 50 Hz, 1 min |
| Operating voltage, UL | 600 V | Operating voltage (UL rating) | 600 V |
| Transfer impedance | 20 mΩ/m at 10 MHz | Characteristic impedance | 100 ± 5 Ω at 100MHz |

Mechanical and material properties of cable

| | | | |
|--------------------------------|--|---------------------------------|----------------------|
| Halogen | Yes | Min. bending radius, repetitive | 7.5 x cable diameter |
| Min. bending radius, once only | 3.5 *diameter | Abrasion resistance | good |
| Resistance to spread of flame | in accordance with IEC 60332-1 / UL 1685 | | |

Plug, left

| | | | |
|-----------|---|--|--|
| Plug left | RJ45, IP20, male contact, straight, plug, Plastic, shielded | | |
|-----------|---|--|--|

Plug, right

| | | | |
|------------|---|--|--|
| Plug right | RJ45, IP20, male contact, straight, plug, Plastic, shielded | | |
|------------|---|--|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-07 | | |

Drawings

Wiring

| RJ45 | | RJ45 |
|------|--------|------|
| 1 | yellow | 1 |
| 2 | orange | 2 |
| 3 | white | 3 |
| 6 | blue | 6 |